



**U.S. TOYO
FAN CORP.**


Finger Guards, Plug Cords, & Jumper Cord

4915 Walnut Grove Ave., San Gabriel, CA 91776 (626) 287-5297 www.ustoyofan.com Email: sales@ustoyofan.com FAX (626) 287-7350

FINGER GUARDS

MATERIAL: C1010 Steel wire or equivalent.
FINISH: Bright nickel chrome
ASSEMBLY: Spot Welded
 Meets UL .25" dia. plug gage test.
DIMENSIONS: Millimeters (inches)
TOLERANCES: Millimeters - .x = $\pm .08$, .xx = ± 0.25
 (inches) --.xx = $\pm .03$, .xxx = $\pm .010$
 Angles - $\pm 1^\circ$

For Use With	P/N	A Dim.	B Dim.	C Dim.	No. of Rings
120 Series	A-120	104.77 (4.125)	115.6 (4.55)	5.6 (.22)	8
92 Series	A-92	82.42 (3.245)	89.4 (3.52)	4.9 (.19)	6
80 Series	A-80	71.37 (2.810)	76.2 (3.00)	4.9 (.19)	5
60 Series	A-60R	50.0 (1.960)	53.1 (2.09)	4.9 (.19)	4
50 Series	A-50	40.0 (1.575)	41.1 (1.62)	4.9 (.19)	3
40 Series	A-40	32.0 (1.260)	29.1 (1.15)	4.9 (.19)	2



PLUG CORDS & JUMPER CORD

MATERIAL: AWG #18 stranded wire, type SPT-1, black PVC, 300V, rated 60° C.
 Rated 10A, 125VAC UL and CSA approved

Plug Cords

Part Numbers & Specifications:

P/N	Length	Plug Config
4001-1	0.9m (3ft)	Right Angle
4001-2	1.8m (6ft)	Right Angle
4004-1	.6m (2ft)	In-Line

Other lengths available upon request.



Jumper Cord

Part Number: 4002

Length 0.3m (1ft)

DISCONTINUED

