


Nylon Insulated Banana Jacks


For standard 0.175" banana plug. Formed brass contact, bright-tinned finish. Comes with nickel-plated nut. **Panel Thickness:** to 0.343". **Current:** 15 A. **Contact Resistance:** 0.010 ohms.



Stock No.	Mfr.'s Type	Color	EACH		
			1-24	25-99	100-999
528-0157	108-0901-001	White	.48	.39	.32
528-0158	108-0902-001	Red	.48	.39	.32
528-0159	108-0903-001	Black	.48	.39	.32
528-0160	108-0904-001	Green	.48	.39	.32
528-0161	108-0906-001	Orange	.48	.39	.32
528-0162	108-0907-001	Yellow	.48	.39	.32
528-0163	108-0908-001	Brown	.48	.39	.32
528-0164	108-0910-001	Blue	.48	.39	.32
528-0165	108-0912-001	Violet	.48	.39	.32
528-0166	108-0913-001	Gray	.48	.39	.32

Insulated Metal-Clad — Military Type Tip Jacks

For 0.080" diameter standard tip plug. Comes with nylon body and nickel-plated brass jacket. Gold-plated turret terminal contact with wrap-around beryllium copper spring. Come with nickel-plated washer and nut. Mounts in panels 0.218" thick. **Breakdown Voltage:** 5700 Vrms. **Current:** 10 A. Conform with MS-16108, Rev. F of MIL-STD-242A and MIL-C-39024/10.



Stock No.	Mfr.'s Type	Color	EACH		
			1-24	25-99	100-999
528-0107	105-0201-200	White	2.25	1.83	1.51
528-0108	105-0202-200	Red	2.25	1.83	1.51
528-0109	105-0203-200	Black	2.25	1.83	1.51
528-0110	105-0204-200	Green	2.25	1.83	1.51
528-0111	105-0207-200	Yellow	2.25	1.83	1.51
528-0112	105-0210-200	Blue	2.25	1.83	1.51

Insulated Metal-Clad Standard Tip Jacks

For 0.080" diameter standard tip plug. Nylon body and nickel-plated threaded, brass jacket. Silver-plated contact is phosphor bronze with slotted terminal. Comes with nickel-plated nut. Mount panels to 0.281" thick. **Breakdown Voltage:** 5700 Vrms minimum. **Current:** 10 A.



Stock No.	Mfr.'s Type	Color	EACH		
			1-24	25-99	100-999
528-0184	105-0251-001	White	.95	.77	.64
528-0185	105-0252-001	Red	.95	.77	.64
528-0186	105-0253-001	Black	.95	.77	.64

Vertical Test Jacks

Mounts through 0.052" hole and requires minimum mounting area. Accepts 0.080" dia. tip plugs. Silver-plated machined or formed beryllium copper contacts. 5 amps.

Machined Contacts

Stock No.	Mfr.'s Type	Color	EACH		
			1-24	25-99	100-999
528-0213	105-0851-001	White	.55	.45	.37
528-0214	105-0852-001	Red	.55	.45	.37
528-0215	105-0853-001	Black	.55	.45	.37

Formed Contacts

528-0219	105-2201-201	White	.49	.40	.33
528-0220	105-2202-201	Red	.49	.40	.33
528-0221	105-2203-201	Black	.49	.40	.33

Rib-Loc® Tip Jacks

Accept standard 0.080" diameter tip plugs. Simply press into mounting hole. Silver-plated terminals. **Current:** 5 A. **Breakdown Voltage:** 3500 Vrms. **Contact Resistance:** 0.005 ohm max.



Stock No.	Mfr.'s Type	Color	EACH		
			1-24	25-99	100-999
528-0208	105-1041-001	White	1.02	.83	.69
528-0209	105-1042-001	Red	1.02	.83	.69
528-0210	105-1043-001	Black	1.02	.83	.69


Insulated Solderless Banana Plugs



For standard 0.166" banana jack. Tapered insulated nylon handle. Connect with wire up to 16 gauge. Nickel-plated brass body with nickel silver plug spring. **Current:** 15 A. **Contact Resistance:** 0.010 ohms.

Stock No.	Mfr.'s Type	Color	EACH		
			1-24	25-99	100-999
528-0147	108-0301-001	White	1.00	.81	.67
528-0302	108-0302-001	Red	1.00	.81	.67
528-0149	108-0303-001	Black	1.00	.81	.67
528-0304	108-0304-001	Green	1.00	.81	.67
528-0306	108-0306-001	Orange	1.00	.81	.67
528-0152	108-0307-001	Yellow	1.00	.81	.67
528-0310	108-0310-001	Blue	1.00	.81	.67
528-0155	108-0312-001	Violet	1.00	.81	.67
528-0156	108-0313-001	Gray	1.00	.81	.67

Insulated Banana Plugs — Hex Body, Solder Stud



For standard banana jacks of 0.166" ID. Wire can be soldered to threaded-stud or flared and held by stud for solderless connection. Accept up to 16-gauge wire. Nylon insulated handle is UL approved for self extinguishing. Plug is nickel-plated brass with nickel silver spring. **Current Rating:** 15 amps. **Breakdown Voltage:** 3500 Vrms minimum. **Contact Resistance:** 0.010 ohms maximum.

Stock No.	Mfr.'s Type	Color	EACH		
			1-24	25-99	100-999
528-0197	108-1762-101	Red	1.68	1.37	1.13
528-0198	108-1763-101	Black	1.68	1.37	1.13

Insulated Standard Tip Jacks

For standard 0.080" diameter tip plug. Nylon body, phosphor bronze contact, tin plated. **Panel Thickness:** 0.437" max. **Current:** 10 A. **Breakdown Voltage:** 5700 Vrms minimum.




Stock No.	Mfr.'s Type	Color	EACH		
			1-24	25-99	100-999
528-0174	105-0801-001	White	.61	.50	.41
528-0175	105-0802-001	Red	.61	.50	.41
528-0176	105-0803-001	Black	.61	.50	.41
528-0179	105-0807-001	Yellow	.61	.50	.41
528-0181	105-0810-001	Blue	.61	.50	.41

Insulated Stacking Dual Banana Plugs (Set Screw)

Molded body incorporates polarity indication and stain relief for wire leads. **Voltage Breakdown:** 3500 Vrms. **Capacity Plug to Plug:** 1.3 pf. **Current** 10 A. **Breakdown Voltage:** 3500 Vrms.

Stock No.	Mfr.'s Type	Color	EACH		
			1-24	25-99	100-999
528-0225	108-0252-001	Red	5.03	4.16	3.30
528-0226	108-0253-001	Black	5.03	4.16	3.30



Panel Mount Uninsulated Banana Plugs and Jacks

Brass body per QQ-B-626D. Plugs have nickel silver springs per QQ-C-585. **Screw Type Plugs (Fig. 1):** 108-0753, for standard jack; 0.125" panel thickness, 14 gauge wire; 15 A. 108-0771, jumbo plug, panel thickness 0.093" to 0.500"; 12 gauge; 40 A. **Jacks Have Nickel Finish (Fig. 2):** Type 108-0740, 0.375" panel thickness; 12 gauge wire; 15 A; pierced lug.

Stock No.	Mfr.'s Type	Fig.	Description	EACH		
				1-24	25-99	100-999
528-0169	108-0753-001	1	Plug, 6-32 screw	1.08	.88	.73
528-0171	108-0771-001	1	Jumbo plug with screw	2.89	2.36	1.86
528-0172	108-0740-001	2	Standard jack	1.17	.96	.79

Insulated Standard Binding Posts


For standard 0.175" diameter banana plug. Flatted, insulated nylon body prevents turning. Silver-plated brass stud has turret termination. Comes with nickel-plated nut. **Current:** 15 A. **Breakdown Voltage:** 5700 Vrms minimum. **Panel Thickness:** 0.261" max.



Stock No.	Mfr.'s Type	Color	EACH		
			1-9	10-49	50-249
528-0137	111-0101-001	White	1.82	1.48	1.23
528-0138	111-0102-001	Red	1.82	1.48	1.23
528-0139	111-0103-001	Black	1.82	1.48	1.23
528-0140	111-0104-001	Green	1.82	1.48	1.23
528-0141	111-0106-001	Orange	1.82	1.48	1.23
528-0142	111-0107-001	Yellow	1.82	1.48	1.23
528-0143	111-0108-001	Brown	1.82	1.48	1.23
528-0144	111-0110-001	Blue	1.82	1.48	1.23
528-0145	111-0112-001	Violet	1.82	1.48	1.23
528-0146	111-0113-001	Gray	1.82	1.48	1.23

Insulated Deluxe Tip Jacks

For 0.080" diameter standard tip plug. Machined silver-plated brass contact with turret terminal and wrap-around beryllium copper spring. Comes with threaded nylon body and nickel-plated nut. Mount in panels to 0.437" thick. **Current:** 10 A. **Breakdown Voltage:** 5700 Vrms minimum.



Stock No.	Mfr.'s Type	Color	EACH		
			1-24	25-99	100-999
528-0117	105-0601-001	White	1.07	.87	.72
528-0118	105-0602-001	Red	1.07	.87	.72
528-0119	105-0603-001	Black	1.07	.87	.72
528-0120	105-0604-001	Green	1.07	.87	.72
528-0122	105-0607-001	Yellow	1.07	.87	.72
528-0124	105-0610-001	Blue	1.07	.87	.72

Insulated Tip Jacks with Sleeve Assembly

For standard 0.080" diameter tip plug. Machined, silver-plated brass contact with turret terminal and wrap-around beryllium copper spring. Assembled body and handle are nylon. For panel thicknesses to 0.125"; 10 A. **Contact Resistance:** 0.010 ohms.

Stock No.	Mfr.'s Type	Color	EACH		
			1-24	25-99	100-999
528-0101	105-0701-001	White	1.35	1.10	.91
528-0102	105-0702-001	Red	1.35	1.10	.91
528-0103	105-0703-001	Black	1.35	1.10	.91

Insulated Solderless Tip Plugs

For 0.080" diameter standard tip jacks. Nylon insulating handle with nickel-plated brass plug contact. Accept wire sizes to 16 gauge. Head recessed to reduce shock hazard. **Current:** 10 A. **Breakdown Voltage:** 3500 Vrms.



Stock No.	Mfr.'s Type	Color	EACH		
			1-24	25-99	100-999
528-0127	105-0301-001	White	.74	.60	.49
528-0128	105-0302-001	Red	.74	.60	.49
528-0129	105-0303-001	Black	.74	.60	.49
528-0130	105-0304-001	Green	.74	.60	.49