



Cordless - Drill and Drivers - 12 Volt 13 mm Cordless Drill Driver

DC756KA



DC756KA Features

- Powerful 12 Volt drill driver for drilling and screwdriving applications
- Compact, lightweight design
- 17 position adjustable torque control for consistent screwdriving into a variety of materials with different screw sizes
- Two speed settings, variable speed and reverse switch for controllable use
- Ergonomically designed trigger and rubber grip
- 13 mm single sleeve keyless chuck with automatic spindle lock for quick and easy bit change with one hand
- Electronic motor brake for added control
- High performance fan cooled motor for maximum power and durability
- All metal gearing for efficient power transmission and longer tool life
- Modular design for easy access to key components and excellent serviceability

DC756KA Specifications

Voltage	12 V
Battery Capacity	NiCd 2.0 Ah
Chuck Capacity	1.5-13 mm
Power Output	240 Watts
No Load Speed	0-400 / 0-1400 rpm
Max Torque	35 Nm
Max. Drilling Capacity [Wood]	28 mm
Max. Drilling Capacity [Metal]	13 mm
Spindle Thread	
Weight	2.0 kg
Length	225 mm
Height	235 mm

DC756KA Standard

- 1 Hour charger
- 2 batteries
- Heavy duty carrying case