

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

170351-0002

Status:

Active

Description:

EXTreme Guardian™ Crimp Receptacle Housing, 2 Circuit, 11.00mm Pitch, 8-10 AWG

Documents:

3D Model

Drawing (PDF)

Product Specification PS-46819-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

TUV

UL

R72130381

E29179

General

Product Family

Series

Application

Product Name

UPC

Crimp Housings

170351

Wire-to-Board, Wire-to-Wire

EXTreme Guardian™

884982274723

Physical

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Compliant

Keying to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Temperature Range - Operating

2

Black

94V-0

Male

No

None

Polyester

7.910/g

1

Bag

No

11.00mm

-40°C to +105°C

Electrical

Current - Maximum per Contact

80A

Material Info


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-46819-001

SD-170351-0002



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

170351Series

Mates With

68790 EXTreme Guardian™ Cable Assembly

Use With

46819 High Power Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION