




| PART NO.                        |                                 | DIM. "A"<br>REF | DIM. "B"<br>REF | DIM. "C"<br>REF | PANEL<br>THICKNESS |
|---------------------------------|---------------------------------|-----------------|-----------------|-----------------|--------------------|
| NYLON 6/6 UL 94<br>V-2 (RMS-01) | NYLON 6/6 UL 94<br>V-0 (RMS-19) |                 |                 |                 |                    |
| WS-A-1-01                       | WS-A-1-19                       | .52 [13.2]      | .19 [4.8]       | .11 [2.8]       | 1/16 [1.6]         |
| WS-A-2-01                       | WS-A-2-19                       | .71 [18]        | .38 [9.7]       |                 |                    |
| WS-A-3-01                       | WS-A-3-19                       | 1.07 [27.2]     | .74 [18.8]      |                 |                    |
| WS-A-4-01                       | WS-A-4-19                       | 1.38 [35]       | 1.05 [26.7]     |                 |                    |
| WS-A-2-1-01                     | WS-A-2-1-19                     | .52 [13.2]      | .19 [4.8]       | .15 [3.8]       | 1/8 [3.2]          |
| WS-A-2-2-01                     | WS-A-2-2-19                     | .71 [18]        | .38 [9.7]       |                 |                    |
| WS-A-2-3-01                     | WS-A-2-3-19                     | 1.07 [27.2]     | .74 [18.8]      |                 |                    |
| WS-A-2-4-01                     | WS-A-2-4-19                     | 1.38 [35]       | 1.05 [26.7]     |                 |                    |



TO SNAP-LOCK IN A .187±.003  
[4.75±0.08] DIA. HOLE, IN A  
PANEL THICKNESS INDICATED

- NOTES:  
 1. COLOR: NATURAL.  
 2. ALTERNATE UNITS FOR REFERENCE ONLY.  
 3. MATERIAL: NYLON 6/6 UVB (RMS-46).  
 COLOR BLACK. AVAILABLE BY SPECIAL ORDER ONLY.  
 TO ORDER REPLACE "-01" WITH "-UVB".

|      |                                    |       |                                 |                  |               |                    |          |           |                |            |
|------|------------------------------------|-------|---------------------------------|------------------|---------------|--------------------|----------|-----------|----------------|------------|
|      |                                    |       | TITLE: WIRE SADDLE W/ ARROWHEAD |                  |               |                    |          |           | DWG IN IN [MM] |            |
| F    | SEE CO 200341 FOR CHANGES          | SK    | 03/17/09                        | FILE #: WS-A     | DWN: SK       | APP: RT            | FINAL    |           |                |            |
| E    | SEE CO 200033 FOR CHANGES          | SK    | 09/25/07                        | SHEET: 1 OF 1    | SHEET SIZE: A | DT: 06/13/07       | CHKD: RG | PART #    |                | PRINT TYPE |
| D    | REDRAWN, SEE ECN #1333 FOR CHANGES | SK    | 06/13/07                        | RE: RICHCO, INC. |               | RICHCO, INC.       |          | SEE TABLE |                | CA         |
| -    | SEE ENGINEERING FOR REV A-C        | -     | ----                            |                  |               | ENG@RICHCO-INC.COM |          |           |                |            |
| REV. | DESCRIPTION                        | ENGR. | DATE                            |                  |               | (773) 539-4060     |          |           |                |            |

CREATED USING  
SOLIDWORKS  
TOLERANCES  
UNLESS NOTED  
XX=±.010  
XXX=±.005  
FRAC.=±1/64  
ANG.=±1°