


Part Number: 336

Type	Size	Rating	Description
Incandescent	T6	14V 80mA	T-1¾ Midget Groove Lamp



Dimensions in millimetres

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
14	72	80	88	4.7	6.3	7.9	1,500

Notes:

- 1

Base Type

Nickel plated S5.7s
- 2

Filament Shape

C-2F
- 3

Lamp Marking

CML 336 14V 80mA
- 4

Environmental

RoHS & REACH SVHC compliant