




REV.	DATE	DESCRIPTION
A	01/25/04	UPDATE DRAWING FORMAT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
7						DRAWN	G.R.S.						01/25/04
6						CHECKED							
5	HEX NUT	BRASS	GOLD	1					PART DESCRIPTION				
4	LOCK WASHER	BRASS	GOLD	1					SMA BULKHEAD RECEPT. JACK				
3	CONTACT PIN	BER. COPPER	GOLD	1				PART NO.					
2	INSULATOR	TEFLON	NATURAL	1				132139					
1	BODY	BRASS	GOLD	1				DWG. NO. 132139.DWG					
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE	C:/132/132139.DWG		REV. A	SIZE A	SCALE NA	