

# "BNC" Adapters

These sturdy within-series BNC adapters are available in all standard designs. Additionally, several unique constructions compliment the product group and allow adaptations for every conceivable application. All connector bodies are plated with bright nickel. Male contacts are brass, female contacts are phosphor bronze. All contacts are plated with 5 micro inches of gold.

| Part Number | Description                                                  | Fig. No. |
|-------------|--------------------------------------------------------------|----------|
| 330A505     | Male/ Male Inline Barrel Splice                              | 35       |
| 332A505     | Female/Female Inline Splice                                  | 36       |
| 335A544     | Female/Female Inline Bulkhead Mount (Grounded)               | 37       |
| 335R544     | Female/Female Inline Isolated Bulkhead (Metal Outer Thread)  | 37       |
| 343A205F    | Crimp "T" Adapter for RG58 Cable                             | 41       |
| 343A205G    | Crimp "T" Adapter for RG59, 62 Cables                        | 41       |
| 343A505     | Female/Male/Female "T" Adapter (Yes, it runs with Netware™ ) | 38       |
| 345A505     | Female/Female/Female "T" Adapter                             | 39       |
| 351A505     | Female/Male Right Angle Adapter                              | 40       |
| 383U505     | The Goalie™                                                  | 42       |
| 383U205F    | The Goalie Brute™ Crimp Version for RG58 Cable               | 45       |
| 383U205G    | The Goalie Brute™ Crimp Version for RG59, 62 Cables          | 45       |
| 383K505*    | The Goalie Brute™                                            | 43       |
| 383P505*    | The Insulated Goalie                                         | 44       |
| 353U205F*   | Male/Female/Female Right Angle Double-Down™Crimp for RG58    | 49       |
| 353U205G*   | Male/Female/Female Right Angle Double-Down™ Type for RG59    | 49       |
| 353U505*    | Male/Female/Female Right Angle Double-Down™                  | 48       |
| 393U205F*   | Male/Female/Female Straight Double-Down™Crimp for RG58       | 47       |
| 393U205G*   | Male/Female/Female Straight Double-Down™Crimp for RG59       | 47       |
| 393U505*    | Male/Female/Female Straight Double-Down™                     | 46       |




Fig. 38




Fig. 39




Fig. 40




Fig. 42




Fig. 43




Fig. 44




Fig. 35




Fig. 36

Fig. 37




Fig. 48




Fig. 46




Fig. 41




Fig. 49




Fig. 45




Fig. 47

## Specialty LAN Adapters

Double Down™ adapters are designed to allow parallel cables entering a patch panel, or a BNC LAN terminal port to be guided at a right angle to the input jack. Two versions accomplish this: one is a right angle with side-by-side jacks for areas with little rear clearance, and the other is a straight version for installations where width between panel jacks is limited. Crimp types are for permanent installations. Goalie, and Goalie Brute allow parallel cable 90° entry which require a minimum of rotational cable space.

