






示意图 SCHEMATIC



安装孔 PIERCING PLAN

④ 规格 Specifications

额定负荷 Ratings	DC 30 V 0.3 A
初期接触电阻 Initial Contact Resistance	30 mΩ Max.
绝缘电阻 Insulation Resistance	DC 500 V 60 Sec. 100 MΩ Min.
抗电强度 Dielectric	AC 500 V (50~60HZ) 60 Sec.

操作力 Operating Force (gf)	A → B B → C	C → B B → A
	200±100	250±100
负荷寿命 Operating Life With Load	10,000 次 Cycles	

7	钢珠 STEEL BALL	SUS	2	NATURAL
6	弹簧 SPRING	SUS	1	NATURAL
5	端子 TERMINAL	C2680R④	8	Ag PLATED
4	基板 TERMINAL BASE	PHENOL RESIN	1	YELLOW
3	接触片 CONTACT	C5210R④	2	Ag CLAD
2	胶柄 KNOB	P O M	1	G 2 - 9
1	铁壳 FRAME	S P C C	1	Ni PLATED
序 NO.	零件 PART	材料 MATERIAL	数量 QTY	备注 REMARKS

A01	ADD: 规格 Specifications 见 ④	王光云	06-05-05
	C2680R-EH → C2680R 见 ④		
	C5210R-EH/Ag CLAD → C5210R 见 ④		
01		赖立辉	12 MAR 93
标号 REV	内容 DESCRIPTION	签名 SIGN.	日期 DATE
DWG NO. ITEM0177			

TOLERANCES UNLESS OTHERWISE SPEC.		TITLE	SLIDE SWITCH	ITEM NO	SS-23E06-G
UNDER 1	± 0.10	DRAWN	王光云	VERSION	A01
1 - 10	± 0.30	REVIEWED	张念明	SCALE	PAGE 1 OF 1
OVER 10	± 0.50	APPROVED	林高全	PROJECTION	UNIT mm

COMAX ELECTRONICS (HUIZHOU) CO.,LTD.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

C&K Components:

[SS-23E06-G 5](#)