


Pin Type Lithium Batteries (BR Series): Individual Specifications

BR425


■ Dimensions(mm)




■ Specification

Nominal voltage (V)	3
Nominal capacity (mAh)	25
Continuous standard load (mA)	0.5
Operating temperature (C)	-20 ~ +60


■ Temperature Characteristics



■ Operating voltage vs. load resistance (voltage at 50% discharge depth)




■ Capacity vs. load resistance



BR435


■ Dimensions(mm)




■ Specification

Nominal voltage (V)	3
Nominal capacity (mAh)	50
Continuous standard load (mA)	1
Operating temperature (C)	-20 ~ +60


■ Temperature Characteristics



■ Operating voltage vs. load resistance (voltage at 50% discharge depth)



■ Capacity vs. load resistance



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

[BR425](#) [BR435](#)