




PIN OUT

(DB9M)J1

J2(DB9F)

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- SHELL
- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- SHELL

- NOTES:
1. WIRE: 28AWG 9C+1 AL/MY OD=5.0MM
2. CONN: J1-DB9P MALE MOLDED TYPE W/TS
- J2-DB9P FEMALE MOLDED TYPE W/TS+NUTS
3. SCREW: 4*30.5MM(#4-40 UNC)
4. NUT: 4.75*6MM(#4-40 UNC)
5. INSIDE&OUTSIDE: MOLDING
6. JACKET & OUTSIDE MOLD PVC COLOR : IVORY
7. LENGTH: SEE THE TABLE
8. PACKING: W/CLEAR POLYBAG(W/MADE IN CHINA
- ELECTRICAL TEST:
- 1)100% OPEN SHORT TEST
- 2)INSULATOR RESISTANCE:1M Ω MIN

G.W. NO	CUS NO.	LENGTH
HC8112A0000000000		10000MM $\pm$ 100MM

1-0		MAR-29-2007	
REV	DESCRIPTION	DATE	ECN NO.

DWG NAME:	IBM PC MONITOR EXT CABLE
G. W. NO:	SEE THE TABLE
CUS NO:	
CUS. ID:	
DWG. NO:	DB9 M-F-04

Rohs Compliant

SHEET:	1/1	TOLERANCE:	. X $\pm$ 0.40	UNIT:	mm
			. XX	DRAW. BY:	
				CHECKED	
				APPROVE	