

Fiber optic cables - VS-P1212-P1212-C1001/ 2,0 - 1608867

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled PROFINET-fiber optic cable, round cable, HCS fiber 200/230 µm, SCRJ/IP67 push-pull metal housing on SCRJ/IP67 push-pull metal housing, for installation inside buildings, length: 2 m



Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	222.22 GRM
Custom tariff number	85447000
Country of origin	Germany

Technical data

Mechanical characteristics

Number of positions	2
Connection profile	SCRJ in acc. with IEC 61754-24
Locking type	Push Pull
Fiber	200/230 µm
Number of fibers	2.00
Insertion/withdrawal cycles	≥ 500
Cable diameter	7.50 mm
Type of cable	Round cable
Length of cable	2 m
Color	silver

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C (cable, fixed installation)
	-10 °C ... 60 °C (cable, flexible installation)
	Plug / socket
Degree of protection	IP65/IP67

Fiber optic cables - VS-P1212-P1212-C1001/ 2,0 - 1608867

Technical data

Material data

Housing material	Zinc die-cast
Material, O-ring	NBR
Cable seal material	TPE
Outer sheath, material	LSFH
External sheath, color	green-yellow RAL 6018
Ferrule holder color	Red

Optical characteristics

Attenuation	≤ 1.2 dB (With 850 nm)
-------------	------------------------

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27061803
eCl@ss 6.0	27061090
eCl@ss 7.0	27061090

ETIM

ETIM 3.0	EC000034
ETIM 4.0	EC001476
ETIM 5.0	EC000034


UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501


Drawings

Fiber optic cables - VS-P1212-P1212-C1001/ 2,0 - 1608867

Schematic diagram




Schematic diagram




Pin assignment plug SCRJ

Pin assignment plug SCRJ

Dimensioned drawing



Dimensioned drawing



SCRJ Push-Pull connector, IP67

SCRJ Push-Pull connector, IP67