


## Knobs, Molded Phenolic

### PH SERIES



PH15181/4



| Tyco        |            | Straight Knurl Less Indicator Line |            |            |            |            |            |
|-------------|------------|------------------------------------|------------|------------|------------|------------|------------|
| Electronics | Alcoswitch | A                                  | B          | C          | D          | E          | F          |
| 1437624-2   | PH15181/4  | .996(25.3)                         | .972(24.7) | .799(20.3) | .472(12.0) | .669(17.0) | .157(3.99) |


### PK SERIES



PK50B1/8



PK701/4




| Tyco        |            | Straight Knurl with Dot Indicator on Skirt |            |             |            |            |             |
|-------------|------------|--------------------------------------------|------------|-------------|------------|------------|-------------|
| Electronics | Alcoswitch | A                                          | B          | C           | D          | E          | F           |
| 1437624-7   | PK50B1/8   | .748(19.0)                                 | .570(14.5) | .500(12.70) | .055(1.40) | .460(11.7) | .550(13.97) |
| 1437624-6   | PK50B1/4   | .748(19.0)                                 | .570(14.5) | .500(12.70) | .055(1.40) | .460(11.7) | .550(13.97) |
| 1437624-8   | PK70B1/4   | .984(25.0)                                 | .728(18.5) | .710(18.03) | .079(2.01) | .500(12.7) | .590(14.99) |
| 1437624-9   | PK90B1/4   | 1.25(31.8)                                 | .985(25.0) | .870(22.01) | .098(2.49) | .470(11.9) | .595(15.10) |

### PK SERIES




PK1100B1/4



| Tyco        |            | Serrated with Dot Indicator on Top |            |             |            |             |            |
|-------------|------------|------------------------------------|------------|-------------|------------|-------------|------------|
| Electronics | Alcoswitch | A                                  | B          | C           | D          | E           | F          |
| 1437624-4   | PK1100B1/8 | .700(17.8)                         | .643(16.3) | .565(14.35) | .125(3.18) | .453(11.51) | .530(13.5) |

## Knobs, Molded Phenolic



### PKA SERIES




PKA50B1/4



PKA90B1/4

| Tyco Electronics Alcoswitch |           | Ribbed with Line Indicator on Skirt |            |            |            |            |            |
|-----------------------------|-----------|-------------------------------------|------------|------------|------------|------------|------------|
|                             |           | A                                   | B          | C          | D          | E          | F          |
| 1-1437624-1                 | PKA50B1/8 | .795(20.2)                          | .580(14.7) | .540(13.7) | .080(2.03) | .450(11.4) | .590(15.0) |
| 1-1437624-0                 | PKA50B1/4 | .795(20.2)                          | .580(14.7) | .540(13.7) | .080(2.03) | .450(11.4) | .590(15.0) |
| 1-1437624-4                 | PKA55B1/8 | .780(19.8)                          | .580(14.7) | .475(12.1) | .135(3.43) | .585(14.9) | .675(17.2) |
| 1-1437624-3                 | PKA55B1/4 | .780(19.8)                          | .580(14.7) | .475(12.1) | .135(3.43) | .585(14.9) | .675(17.2) |
| 1-1437624-5                 | PKA70B1/4 | .980(24.9)                          | .740(18.8) | .680(17.3) | .118(3.00) | .650(16.5) | .750(19.1) |
| 1-1437624-7                 | PKA90B1/4 | 1.375(34.9)                         | .970(24.6) | .670(17.0) | .195(4.95) | .750(19.1) | .840(21.3) |



### PKAP SERIES



PKAP50B1/8



PKAP90B1/4

| Tyco Electronics Alcoswitch |            | Ribbed with Skirt and Pointer with Indicator Line |            |            |            |            |             |
|-----------------------------|------------|---------------------------------------------------|------------|------------|------------|------------|-------------|
|                             |            | A                                                 | B          | C          | D          | E          | F           |
| 1-1437624-8                 | PKAP50B1/4 | .787(20.0)                                        | .693(17.6) | .508(12.9) | .082(2.08) | .579(14.7) | .689(17.5)  |
| 1-1437624-9                 | PKAP50B1/8 | .787(20.0)                                        | .693(17.6) | .508(12.9) | .082(2.08) | .579(14.7) | .689(17.5)  |
| 2-1437624-0                 | PKAP70B1/4 | .976(24.8)                                        | .874(22.1) | .668(17.0) | .158(4.01) | .634(16.1) | .737(18.72) |

**K**


**P Series**

## Knobs, Molded Phenolic

### PKB SERIES



PKB90B1/4



|             |            | Fluted with Indicator Line On Skirt |            |            |           |            |            |
|-------------|------------|-------------------------------------|------------|------------|-----------|------------|------------|
| Tyco        |            | A                                   | B          | C          | D         | E          | F          |
| Electronics | Alcoswitch |                                     |            |            |           |            |            |
| 2-1437624-3 | PKB70B1/4  | 1.12(28.3)                          | .750(19.1) | .670(17.0) | .118(3.0) | .490(12.5) | .600(15.2) |
| 2-1437624-4 | PKB90B1/4  | 1.50(38.1)                          | 1.02(25.8) | .800(20.3) | .118(3.0) | .705(17.9) | .820(20.8) |


### PKD SERIES



PKD60B1/4



PKD100B1/4



|             |            | Straight Knurl Aluminum Skirt w/Arrow Indicator |            |            |           |            |            |
|-------------|------------|-------------------------------------------------|------------|------------|-----------|------------|------------|
| Tyco        |            | A                                               | B          | C          | D         | E          | F          |
| Electronics | Alcoswitch |                                                 |            |            |           |            |            |
| 2-1437624-8 | PKD60B1/8  | .780(19.8)                                      | .566(14.4) | .487(12.4) | .059(1.5) | .492(12.5) | .563(14.3) |
| 2-1437624-7 | PKD60B1/4  | .780(19.8)                                      | .566(14.4) | .487(12.4) | .059(1.5) | .492(12.5) | .563(14.3) |
| 3-1437624-1 | PKD70B1/4  | 1.02(25.9)                                      | .750(19.1) | .700(17.8) | .080(2.0) | .490(12.5) | .610(15.5) |
| 2-1437624-5 | PKD100B1/4 | 1.29(32.8)                                      | 1.00(25.4) | .865(22.0) | .050(1.3) | .500(12.7) | .590(15.0) |


### PKD SERIES



PKD60B101/8




PKD100B101/4



|             |              | Straight Knurl Skirt w/0-10 Numerals |            |            |           |            |            |
|-------------|--------------|--------------------------------------|------------|------------|-----------|------------|------------|
| Tyco        |              | A                                    | B          | C          | D         | E          | F          |
| Electronics | Alcoswitch   |                                      |            |            |           |            |            |
| 3-1437624-0 | PKD60B101/8  | .780(19.8)                           | .566(14.4) | .487(12.4) | .059(1.5) | .492(12.5) | .563(14.3) |
| 2-1437624-9 | PKD60B101/4  | .780(19.8)                           | .566(14.4) | .487(12.4) | .059(1.5) | .492(12.5) | .563(14.3) |
| 3-1437624-2 | PKD70B101/4  | 1.02(25.9)                           | .750(19.1) | .700(17.8) | .080(2.0) | .490(12.5) | .610(15.5) |
| 2-1437624-6 | PKD100B101/4 | 1.29(32.8)                           | 1.00(25.4) | .865(22.0) | .050(1.3) | .500(12.7) | .590(15.0) |

## Knobs, Molded Phenolic




### PKDT SERIES



PKDT100B1/4

| Black Spin Cap with "Diamond Cut" and Arrow Indicator |             |            |            |            |            |            |            |
|-------------------------------------------------------|-------------|------------|------------|------------|------------|------------|------------|
| Tyco Electronics                                      | Alcoswitch  | A          | B          | C          | D          | E          | F          |
| 3-1437624-9                                           | PKDT70B1/4  | 1.03(26.0) | .738(18.8) | .720(18.3) | .098(2.49) | .500(12.7) | .635(16.1) |
| 3-1437624-3                                           | PKDT100B1/4 | 1.29(32.8) | 1.02(25.9) | .860(21.8) | .042(1.07) | .500(12.7) | .638(16.2) |




### PKDT SERIES



PKDT100B101/4

| Black Spin Cap with "Diamond Cut" & 0-10 Numerals |               |            |            |            |            |            |            |
|---------------------------------------------------|---------------|------------|------------|------------|------------|------------|------------|
| Tyco Electronics                                  | Alcoswitch    | A          | B          | C          | D          | E          | F          |
| 3-1437624-8                                       | PKDT60B101/8  | .778(19.8) | .605(15.4) | .560(12.5) | .060(1.53) | .392(9.96) | .562(14.3) |
| 4-1437624-0                                       | PKDT70B101/4  | 1.03(26.0) | .738(18.8) | .720(18.3) | .098(2.49) | .500(12.7) | .635(16.1) |
| 3-1437624-4                                       | PKDT100B101/4 | 1.29(32.8) | 1.02(25.9) | .860(21.8) | .042(1.07) | .500(12.7) | .638(16.2) |




### PKE SERIES



PKE90B1/4

| Fluted with Indicator Line |            |            |            |            |            |
|----------------------------|------------|------------|------------|------------|------------|
| Tyco Electronics           | Alcoswitch | A          | B          | C          | D          |
| 4-1437624-4                | PKE60B1/8  | .626(15.9) | .472(12.0) | .091(2.31) | .394(10.0) |
| 4-1437624-3                | PKE60B1/4  | .626(15.9) | .472(12.0) | .091(2.31) | .394(10.0) |
| 4-1437624-5                | PKE90B1/4  | .890(22.6) | .724(18.4) | .098(2.49) | .480(12.2) |



### PKES SERIES



PKES60B1/4



PKES70B1/4


| Fluted with Skirt and Indicator Line |             |            |            |            |            |            |
|--------------------------------------|-------------|------------|------------|------------|------------|------------|
| Tyco Electronics                     | Alcoswitch  | A          | B          | C          | D          | F          |
| 5-1437624-1                          | PKES60B1/8  | .748(19.0) | .618(15.7) | .460(11.7) | .090(2.29) | .470(11.9) |
| 5-1437624-0                          | PKES60B1/4  | .748(19.0) | .618(15.7) | .460(11.7) | .090(2.29) | .470(11.9) |
| 5-1437624-2                          | PKES70B1/4  | .855(21.7) | .744(18.9) | .705(17.9) | .080(2.03) | .526(13.4) |
| 5-1437624-3                          | PKES90B1/4  | 1.01(25.7) | .889(22.6) | .846(21.5) | .079(2.01) | .570(14.5) |
| 4-1437624-6                          | PKES120B1/4 | 1.30(32.9) | 1.16(29.5) | 1.02(25.9) | .118(3.00) | .628(16.0) |
| 4-1437624-7                          | PKES140B1/4 | 1.50(38.1) | 1.37(34.9) | 1.22(30.9) | .118(3.00) | .693(17.6) |
| 4-1437624-8                          | PKES150B1/4 | 1.77(44.9) | 1.55(39.4) | 1.41(35.9) | .118(3.00) | .831(21.1) |

## Knobs, Molded Phenolic

### PKF SERIES



PKF50B1/8




| Tyco Plain Quadrate with Indicator Line & Arrow |            |            |             |             |            |
|-------------------------------------------------|------------|------------|-------------|-------------|------------|
| Electronics                                     | Alcoswitch | A          | B           | C           | D          |
| 5-1437624-5                                     | PKF50B1/8  | .670(17.0) | .454(11.53) | .570(14.48) | .520(13.2) |

### PKG SERIES



PKG40B1/8




| Ribbed with Indicator Line       |            |            |            |            |            |             |            |
|----------------------------------|------------|------------|------------|------------|------------|-------------|------------|
| Tyco                             |            | A          | B          | C          | D          | E           | F          |
| Electronics                      | Alcoswitch |            |            |            |            |             |            |
| 5-1437624-9                      | *PKG40B1/8 | .437(11.1) | .410(10.4) | .304(7.72) | .079(2.00) | .385(9.78)  | .472(12.0) |
| 6-1437624-1                      | PKG50B1/8  | .551(14.0) | .500(12.7) | .442(10.7) | .056(1.42) | .395(10.03) | .512(13.0) |
| 6-1437624-0                      | PKG50B1/4  | .551(14.0) | .500(12.7) | .442(10.7) | .056(1.42) | .395(10.03) | .512(13.0) |
| *Note: Knob uses #4-40 set screw |            |            |            |            |            |             |            |

\*Note: Knob uses #4-40 set screw


## Knobs, Molded Phenolic

### PKG SERIES



PKG70B1/8

| Tyco        |            | Ribbed with Indicator Line |            |            |            |            |            |
|-------------|------------|----------------------------|------------|------------|------------|------------|------------|
| Electronics | Alcoswitch | A                          | B          | C          | D          | E          | F          |
| 6-1437624-6 | PKG60B1/8  | .660(16.8)                 | .615(15.6) | .551(14.0) | .080(2.03) | .430(10.9) | .551(14.0) |
| 6-1437624-5 | PKG60B1/4  | .660(16.8)                 | .615(15.6) | .551(14.0) | .080(2.03) | .430(10.9) | .551(14.0) |
| 6-1437624-8 | PKG70B1/8  | .740(18.8)                 | .698(17.7) | .591(15.0) | .080(2.03) | .453(11.5) | .559(14.2) |
| 6-1437624-7 | PKG70B1/4  | .740(18.8)                 | .698(17.7) | .591(15.0) | .080(2.03) | .453(11.5) | .559(14.2) |




### PKG SERIES



PKG90B1/4

| Tyco        |            | Ribbed with Indicator Line |            |            |            |            |             |
|-------------|------------|----------------------------|------------|------------|------------|------------|-------------|
| Electronics | Alcoswitch | A                          | B          | C          | D          | E          | F           |
| 7-1437624-0 | PKG90B1/8  | .862(21.9)                 | .811(20.6) | .710(18.0) | .080(2.03) | .450(11.4) | .550(13.97) |
| 6-1437624-9 | PKG90B1/4  | .862(21.9)                 | .811(20.6) | .710(18.0) | .080(2.03) | .450(11.4) | .550(13.97) |
| 5-1437624-7 | PKG100B1/4 | 1.055(26.80)               | 1.01(25.5) | .920(23.4) | .080(2.03) | .430(10.9) | .555(14.1)  |
| 5-1437624-8 | PKG125B1/4 | 1.248(31.70)               | 1.20(30.4) | .690(17.5) | .080(2.03) | .430(10.9) | .565(14.4)  |




### PKGP SERIES



PKGP70B1/4

| Tyco        |             | Ribbed with Bar Pointers and Indicator Line |            |            |            |            |            |
|-------------|-------------|---------------------------------------------|------------|------------|------------|------------|------------|
| Electronics | Alcoswitch  | A                                           | B          | C          | D          | E          | F          |
| 7-1437624-2 | PKGP70B1/4  | .740(18.8)                                  | .700(17.8) | .590(15.0) | .990(25.2) | .080(2.03) | .460(11.7) |
| 7-1437624-3 | PKGP90B1/4  | .860(21.8)                                  | .810(20.6) | .700(17.8) | 1.28(32.5) | .080(2.03) | .460(11.7) |
| 7-1437624-1 | PKGP100B1/4 | 1.05(26.2)                                  | 1.00(25.4) | .900(22.9) | 1.62(41.2) | .080(2.03) | .480(12.2) |



### PKJ SERIES



PKJ50B1/8

| Tyco        |            | Straight Knurl with Bar Pointers and Indicator Line |            |            |            |            |           |
|-------------|------------|-----------------------------------------------------|------------|------------|------------|------------|-----------|
| Electronics | Alcoswitch | A                                                   | B          | C          | D          | E          | F         |
| 7-1437624-5 | PKJ50B1/8  | .500(12.7)                                          | .512(13.0) | .420(10.7) | .577(14.7) | .429(10.9) | .113(2.9) |
| 7-1437624-4 | *PKJ50B1/4 | .500(12.7)                                          | .512(13.0) | .420(10.7) | .577(14.7) | .429(10.9) | .113(2.9) |
| 7-1437624-6 | PKJ60B1/4  | .630(16.0)                                          | .530(13.5) | .468(11.9) | .758(19.3) | .440(11.2) | .110(2.8) |
| 7-1437624-7 | PKJ70B1/4  | .760(19.3)                                          | .555(14.1) | .545(13.8) | .915(23.2) | .450(11.4) | .118(3.0) |

\*Note: Knob uses #4-40 set screw



PKJ70B1/4

## Knobs, Molded Phenolic


### PKJT SERIES



PKJT50B1/4



PKJT70B1/4




| Straight Knurl with Bar Pointer & Indicator Line and Aluminum Spin Cap<br>Tyco |             |            |            |            |            |            |            |
|--------------------------------------------------------------------------------|-------------|------------|------------|------------|------------|------------|------------|
| Electronics                                                                    | Alcoswitch  | A          | B          | C          | D          | E          | F          |
| 7-1437624-9                                                                    | PKJT50B1/8  | .515(13.1) | .585(14.9) | .350(8.89) | .595(15.1) | .414(10.5) | .130(3.30) |
| 7-1437624-8                                                                    | *PKJT50B1/4 | .515(13.1) | .585(14.9) | .350(8.89) | .595(15.1) | .414(10.5) | .130(3.30) |
| 8-1437624-0                                                                    | PKJT60B1/4  | .640(16.3) | .605(15.4) | .470(11.9) | .760(19.3) | .445(11.3) | .118(3.00) |
| 8-1437624-1                                                                    | PKJT70B1/4  | .760(19.3) | .625(15.9) | .550(14.0) | .915(23.2) | .445(11.3) | .118(3.00) |

\*Knob uses #4-40 set screw.

### PKNT SERIES



PKNT60B1/4




| Black Spin Cap with "Diamond Cut" Less Indicator<br>Tyco |            |            |            |            |            |            |            |
|----------------------------------------------------------|------------|------------|------------|------------|------------|------------|------------|
| Electronics                                              | Alcoswitch | A          | B          | C          | D          | E          | F          |
| 8-1437624-6                                              | PKNT60B1/8 | .591(15.0) | .579(14.7) | .394(10.0) | .079(2.01) | .394(10.0) | .472(11.9) |
| 8-1437624-5                                              | PKNT60B1/4 | .591(15.0) | .579(14.7) | .394(10.0) | .079(2.01) | .394(10.0) | .472(11.9) |
| 8-1437624-7                                              | PKNT70B1/4 | .787(19.9) | .764(19.4) | .571(14.5) | .098(2.49) | .492(12.5) | .591(14.7) |
| 8-1437624-8                                              | PKNT90B1/4 | .984(25.0) | .957(24.3) | .748(19.0) | .098(2.49) | .591(15.0) | .689(17.5) |

### PKN SERIES




PKN60B1/8



| Line Indicator on Natural Aluminum Spin Cap<br>Tyco |            |            |            |            |            |            |            |
|-----------------------------------------------------|------------|------------|------------|------------|------------|------------|------------|
| Electronics                                         | Alcoswitch | A          | B          | C          | D          | E          | F          |
| 8-1437624-2                                         | PKN60B1/8  | .591(15.0) | .579(14.7) | .394(10.0) | .079(2.01) | .394(10.0) | .453(11.5) |
|                                                     | PKN60B1/4  | .591(15.0) | .579(14.7) | .394(10.0) | .079(2.01) | .394(10.0) | .453(11.5) |
| 8-1437624-3                                         | PKN70B1/4  | .787(20.0) | .764(19.4) | .571(14.5) | .098(2.49) | .492(12.5) | .591(15.0) |
| 8-1437624-4                                         | PKN90B1/4  | .984(25.0) | .957(24.3) | .748(19.0) | .098(2.49) | .591(15.0) | .689(17.5) |

## Knobs, Molded Phenolic

### PKS SERIES



PKS1104B1/4


|                  |             | Straight Knurl with Indicator Line on Skirt |            |            |            |             |            |
|------------------|-------------|---------------------------------------------|------------|------------|------------|-------------|------------|
| Tyco Electronics | Alcoswitch  | A                                           | B          | C          | D          | E           | F          |
| 9-1437624-5      | PKS1104B1/4 | 1.12(28.5)                                  | .567(14.4) | .620(15.8) | .090(2.29) | .510(12.95) | .670(17.0) |

### PKS SERIES


| Straight Knurl Aluminum Skirt Has Line or 0-9 Numbers |               |            |            |            |            |            |            |         |
|-------------------------------------------------------|---------------|------------|------------|------------|------------|------------|------------|---------|
| Tyco Electronics                                      | Alcoswitch    | A          | B          | C          | D          | E          | F          | Marking |
| 9-1437624-4                                           | PKS1103B101/4 | 1.17(29.6) | .571(14.5) | .620(15.7) | .098(2.49) | .516(13.1) | .670(17.0) | Numbers |
| 9-1437624-7                                           | PKS1106B1/4   | 1.17(29.6) | .571(14.5) | .618(15.7) | .098(2.49) | .516(13.1) | .670(17.0) | Line    |
| 9-1437624-6                                           | PKS1105B101/4 | 1.17(29.6) | .571(14.5) | .618(15.7) | .098(2.49) | .516(13.1) | .670(17.0) | Numbers |





PKS1106B1/4



PKS1103B101/4




PKS1105B101/4



### PKS SERIES

SPUN ALUMINUM INLAY



0-10



+5-5



0-9



Indicator Line



PKS1132B51/4

| Choice of Indicator Line or 0-9, 0-10, -5+5 Numerals |               |            |            |            |            |             |            |                |
|------------------------------------------------------|---------------|------------|------------|------------|------------|-------------|------------|----------------|
| Tyco                                                 |               |            |            |            |            |             |            |                |
| Electronics                                          | Alcoswitch    | A          | B          | C          | D          | E           | F          | Marking        |
| 1437625-1                                            | PKS1132B51/4  | 1.18(30.0) | .551(14.0) | .551(14.0) | .118(30.0) | .615(15.62) | .748(19.0) | +5-0-5         |
| 1437625-2                                            | PKS1132B91/4  | 1.18(30.0) | .551(14.0) | .551(14.0) | .118(30.0) | .615(15.62) | .748(19.0) | 0-9            |
| 9-1437624-9                                          | PKS1132B101/4 | 1.18(30.0) | .551(14.0) | .551(14.0) | .118(30.0) | .615(15.62) | .748(19.0) | 0-10           |
| 9-1437624-8                                          | *PKS1132B1/4  | 1.18(30.0) | .551(14.0) | .551(14.0) | .118(30.0) | .615(15.62) | .748(19.0) | Indicator Line |
| *1 Set screw 180° from indicator line.               |               |            |            |            |            |             |            |                |

\*1 Set screw 180° from indicator line.




PKS1132B91/4

## Knobs, Molded Phenolic

### PKS SERIES



PKS90B1/4




| Tyco<br>Electronics Alcoswitch Straight Knurl with Aluminum Skirt Choice of Arrow or 1-10 Numbers |             |            |            |            |            |            |            |         |
|---------------------------------------------------------------------------------------------------|-------------|------------|------------|------------|------------|------------|------------|---------|
|                                                                                                   |             | A          | B          | C          | D          | E          | F          | Marking |
| 1437625-5                                                                                         | PKS90B1/4   | 1.42(36.1) | .917(23.3) | .780(19.8) | .065(1.65) | .490(12.5) | .596(15.1) | Arrow   |
| 1437625-6                                                                                         | PKS90B101/4 | 1.42(36.1) | .917(23.3) | .780(19.8) | .065(1.65) | .490(12.5) | .596(15.1) | Numbers |

### PKX SERIES



PKX50B1/8




| Tyco<br>Electronics Alcoswitch Ribbed Body, Matte Finish with White Square Indicator on Top |           |            |            |            |            |             |            |
|---------------------------------------------------------------------------------------------|-----------|------------|------------|------------|------------|-------------|------------|
|                                                                                             |           | A          | B          | C          | D          | E           | F          |
| 1-1437625-5                                                                                 | PKX50B1/8 | .590(15.0) | .472(12.0) | .374(9.49) | .059(1.50) | .463(11.76) | .551(14.0) |
| 1-1437625-4                                                                                 | PKX50B1/4 | .590(15.0) | .472(12.0) | .374(9.49) | .059(1.50) | .463(11.76) | .551(14.0) |
| 1-1437625-7                                                                                 | PKX60B1/8 | .787(20.0) | .625(15.9) | .472(12.0) | .078(1.98) | .510(13.0)  | .598(15.2) |
| 1-1437625-6                                                                                 | PKX60B1/4 | .787(20.0) | .625(15.9) | .472(12.0) | .078(1.98) | .510(13.0)  | .598(15.2) |

### PKX SERIES




PKX110B1/4



| Tyco<br>Electronics Alcoswitch Ribbed Body, Matte Finish with White Square Indicator on Top |            |            |              |             |            |             |             |
|---------------------------------------------------------------------------------------------|------------|------------|--------------|-------------|------------|-------------|-------------|
|                                                                                             |            | A          | B            | C           | D          | E           | F           |
| 1-1437625-1                                                                                 | PKX100B1/4 | 1.17(29.7) | .970(24.6)   | .780(19.81) | .114(2.90) | .570(14.48) | .674(17.12) |
| 1-1437625-2                                                                                 | PKX110B1/4 | 1.37(34.8) | 1.120(28.45) | .940(23.88) | .100(2.54) | .527(13.38) | .705(17.91) |
| 1-1437625-3                                                                                 | PKX130B1/4 | 1.57(40.0) | 1.308(33.22) | 1.09(27.6)  | .118(3.00) | .623(15.82) | .750(19.05) |

## Knob Accessories

### ACCESSORIES



KR1

|             |                   | Shaft Hole Size Adaptors |            |            |            |            |            |
|-------------|-------------------|--------------------------|------------|------------|------------|------------|------------|
| Tyco        | Alcoswitch        | A                        | B          | C          | D          | E          | F          |
| 9-1437627-6 | KR1 (1/4"TO1/8")  | .374(9.50)               | .250(6.35) | .128(3.25) | .122(3.10) | .217(5.51) | .122(3.10) |
| 9-1437627-7 | KR2 (1/4"TO3/16") | .375(9.53)               | .250(6.35) | .190(4.83) | .122(3.10) | .216(5.49) | .123(3.12) |
| 9-1437627-8 | KR3 (1/4"TO4MM)   | .375(9.53)               | .248(6.30) | .161(4.09) | .122(3.10) | .216(5.49) | .123(3.12) |