


Dimensions: mm (In.)



Electrical Specifications:

- Rating: 15A/125VAC, 10A/250VAC
- Contact Resistance: 50mΩ max.
- Insulation Resistance: 100MΩ min. @ 500VDC
- Dielectric Strength: 1500VAC for 1 minute

Mechanical Specifications:

- Circuit: 2P SPST On-Off
- Operating Temperature Range: -20°C to +70°C
- Storage Temperature Range: -20°C to +70°C

Note:

- RoHS Compliant

Rocker Switch
103-R13-72A-EV



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-R13-72A-EV](#)