


REV.	DATE	DESCRIPTION
NC	02/05/08	INITIAL RELEASE



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex										
8						DRAWN	G.R.S.	02/05/08												
7						CHECKED														
6									PART DESCRIPTION											
5									UHF ANGLE ADAPTER JACK–PLUG											
4									—											
3	CONTACT PIN	BRASS	GOLD	1					PART NO.											
2	INSULATOR	PTFE	NATURAL	1					182134											
1	BODY	BRASS	NICKEL	1																
DESCRIPTION						MATERIAL		FINISH		QTY		CAD FILE		DWG. NO.		REV.		SIZE		SCALE
											C:/1821/182134.DWG		182134.DWG		NC		A		NA	