







REV.	DATE	DESCRIPTION
NC	03/02/00	INITIAL RELEASE
A	11/13/06	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex				
8						DRAWN	G.R.S.					11/13/06
7						CHECKED			PART DESCRIPTION BNC PANEL CRIMP JACK (FOR RG–174/U, 188A, 316/U CABLE)			
6						ISSUED						
5	FERRULE	BRASS	NICKEL	1		SHEET	1 OF 1		PART NO. 112288			
4	SLEEVE	DELTRIN	NATURAL	1								
3	CONTACT PIN	BER. COPPER	GOLD	1					DWG. NO. 112288.DWG			
2	INSULATOR	TEFLON	NATURAL	1								
1	BODY	BRASS	NICKEL	1					REV. A	SIZE A	SCALE NA	
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE C:/112/112288.DWG					