


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190990009](#)
Status: **Active**
Description: InsulKrimp™ Snap Spade Terminal for 18-22 AWG Wire

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-009 \(PDF\)](#)

General	
Product Family	Ring and Spade Terminals
Series	19099
Mil-Spec	N/A
Product Name	InsulKrimp™
Type	Spade Snap
Physical	
Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-2
Insulation	PVC
Material - Plating Mating	Tin
Packaging Type	Bag
Stud Size	5-6 (M3-3.5)
Wire Insulation Diameter	4.40mm (.175") max.
Wire Size AWG	18, 20, 22
Wire Size mm²	0.35 - 0.80
Electrical	
CSA	LR18689
UL	E32244
Material Info	
Old Part Number	AA-2704-06X
Reference - Drawing Numbers	
Product Specification	PS-19902-009
Sales Drawing	AACD20502



*Series
image - Reference only*

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Halogen-Free
Status
Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19099Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	0640010100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050300
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640051200
Hand Crimp Tool	0640010300
Hand Crimp Tool	0640011200

This document was generated on 02/02/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION