

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0503263574](#)
Status: **Obsolete**
Description: Spade Tongue Terminal for 14 and 16 AWG, Closed Insulated Vinyl Flared Barrel, Blue, Stud Size 1/4" (M6), Oxygen-Free Copper, Length 24.50mm (.965")

Documents:
[Drawing \(PDF\)](#)

General

Product Family	Ring and Spade Terminals
Series	50326
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Product Name	VFY (Spade Vinyl Flared)
Type	Spade

Physical

Barrel Type	Closed - Brazed
Color - Resin	Blue
Insulation	PVC
Material - Plating Mating	Tin
Packaging Type	Bag
Stud Size	1/4" (M6)
Wire Size AWG	14, 16
Wire Size mm ²	1.04 - 2.63

Material Info

Reference - Drawing Numbers

Product Specification	PS-50325-002
Sales Drawing	SD-50326-001




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[50326Series](#)