



NOTES:

1. ALL DIMENSION IN MM [INCH]
 2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
 3. TERM. NOS. FOR REF. ONLY
 4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
 5. CONTACT MATERIAL: SILVER PLATING OVER COPPER
 6. OPERATING FORCE: 425 $\pm$ 100 CM/STANDARD
 7. OPERATING TEMP: -30 $^{\circ}$ to 85 $^{\circ}$ C
 8. CIRCUIT DP: 6 POSITIONS, 30 $^{\circ}$ INDEX.
 9. DIELECTRIC STRENGTH: 1000V RMS min.@Seo Level
 10. DESIGNATE MAJOR DIMENSIONS
 11. HARDWARE SUPPLIED ON SWITCH- SEE BELOW
- STOPRING, LOCKWASHER, & HEXNUT.





CONTACT CONFIGURATION

Timing: Non Shorting (BBM)



TERMINATION DETAIL

SCALE 2X



E-SWITCH®				
TITLE		KC-26-A (9.5mm) 01-N-L-S		
B	12821	REVISED NOTE 11	3/6/03	CJB
A	12020	RELEASED FOR PRODUCTION	3/27/02	CJB
REV.	ECN No.	DESCRIPTION	DATE	CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				
SCALE		DATE	DR	DWG
1.5:1		3/27/02	CJB	6523729
				REV
				B