





REV.	DATE	ECR NO.	DESCRIPTION
NC	06/11/97	—	INITIAL RELEASE
A	11/08/08	—	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex					
8						DRAWN	GRS	11/08/08							
7						CHECKED									
6											PART DESCRIPTION				
5	FERRULE	BRASS	NICKEL	1							TNC CRIMP PLUG (FOR 174/U, 316/U CABLE – HIGH FREQUENCY)				
4	BARREL	BRASS	NICKEL	1							PART NO.				
3	CONTACT PIN	BRASS	GOLD	1							122395				
2	INSULATOR	PTFE	NATURAL	1							DWG. NO.				
1	BODY	BRASS	NICKEL	1						SCALE NA					
DESCRIPTION					MATERIAL	FINISH	QTY	CAD FILE							
								C:/122/122395.DWG							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[122395](#)