




VRLA Rechargeable Battery

BP33-12 (BP33-12FR)

Handle Type



FEATURES

- Maintenance free(no water topping-up required).
- No free acid(Non-spillable battery).
- Low self-discharge rate, lower than 3% capacity loss per month.
- Can be used in any orientation(excluding used inverted).
- Absorbent Glass Mat technology for efficient gas recombination.

APPLICATION

- UPS
- Wheelchairs
- Lawn Mowers
- Golf-Carts
- Electronic Medical Equipment



SPECIFICATIONS

Nominal Voltage	12 V
Nominal Capacity	33.0Ah @ 20 hour rate F.V.(1.75V/cell)
Approx. Weight	11250g(24.81lbs.)
Terminals	B7 (Fitting M6 bolt & nut) I2 is optional
Internal Resistance	≤9mΩ (Fully Charged)
Max. Discharge Current	495 A (5 sec.)
Max. Charge Current	9.9 A
Operating Temperature Range	Charge : 0°C~40°C(32°F~104°F) Discharge : -20°C~50°C(-4°F~122°F) Storage. : -20°C~40°C(-4°F~104°F)
Container Material	ABS(UL94-HB, UL94-V0 is optional)

ISO 9001



ISO14001



UL



CE



- IEC 61056-1
- JIS C 8702-1
- GB/T 19639.1

DIMENSION(mm/inch)	OUTER DIMENSIONS	TERMINAL TYPE
Length 210±1.5 (8.27±0.06) Width 129±1.5 (5.08±0.06) Container Height 168±1.5 (6.61±0.06) Total Height B7:179±2.0 (7.05±0.08) I2:168±2.0 (6.61±0.08)		● Terminal B7 ● Terminal I2 [M6 BOLT & NUT] [M6 BOLT] Terminal Hardware Initial Torque: B7/I2(5.5Nm±5%)

Constant power discharge characteristics at 25 °C/77 °F Unit: W

Discharge Time F.V. (V/cell)	5 Min	10 Min	15 Min	30 Min	1 Hr	3 Hr	5 Hr	10 Hr	20 Hr
1.80V	1193	878	704	419	240.2	96.2	66.3	37.06	19.50
1.75V	1381	952	736	435	247.4	98.1	67.3	37.62	19.80
1.70V	1467	986	759	445	251.8	99.0	67.7	37.81	19.90
1.65V	1533	1009	776	451	254.9	99.7	67.9	37.92	19.96
1.60V	1584	1030	792	455	257.4	100.3	68.1	37.92	19.96

Constant current discharge characteristics at 25 °C/77 °F Unit: A

Discharge Time F.V. (V/cell)	5 Min	10 Min	15 Min	30 Min	1 Hr	3 Hr	5 Hr	10 Hr	20 Hr
1.80V	107.5	77.3	61.2	35.5	20.18	8.02	5.53	3.09	1.63
1.75V	126.7	83.8	64.0	36.8	20.79	8.18	5.61	3.13	1.65
1.70V	134.6	86.8	66.0	37.7	21.16	8.25	5.64	3.15	1.66
1.65V	140.7	88.9	67.5	38.2	21.42	8.31	5.66	3.16	1.66
1.60V	145.3	90.6	68.9	38.6	21.63	8.36	5.68	3.16	1.66

All data shall be changed without prior notice, BB reserves the right to explain and update the information contained hereinto.