


Female Crimp Terminal Connectors



Operating Temperature: 75°C max.

Material : Copper
Terminal : PVC
Insulation : TIN
Plating

Best.-Nr.	Typ	WIRE RANGE mm ² / AWG	Suitable connect TAB	T (mm)	DIMENSION					COLOR
				±0.1	B (mm) ±0.2	dø (mm) ±0.2	Dø (mm) ±0.3	L (mm) ±1.0	H (mm) ±0.1	
74 50 98	FDD1.25-110(5)	0.5~1.5mm ² 22~16 AWG	2.8 x 0.5	0.3	3.2	1.7	3.5	19.0	10.0	RED
74 51 10	FDD1.25-110(8)		2.8 x 0.8	0.3	3.2	1.7	3.5	19.0		
74 51 22	FDD1.25-187(5)		4.8 x 0.5	0.35	5.0	1.7	3.5	19.0		
74 51 36	FDD1.25-187(8)		4.8 x 0.8	0.35	5.0	1.7	3.5	19.0		
73 73 68	FDD1.25-205		5.2 x 0.5	0.35	5.7	1.7	3.5	20.0		
74 51 51	FDD1.25-250		6.4 x 0.8	0.4	6.6	1.7	3.5	21.0		
73 74 02	FDD2-110(5)	1.5~2.5mm ² 16~14 AWG	2.8 x 0.5	0.3	3.2	2.3	4.0	19.0	10.0	BLUE
73 74 43	FDD2-110(8)		2.8 x 0.8	0.3	3.2	2.3	4.0	19.0		
74 51 66	FDD2-187(5)		4.8 x 0.5	0.35	5.0	2.3	4.0	19.0		
74 51 80	FDD2-187(8)		4.8 x 0.8	0.35	5.0	2.3	4.0	19.0		
73 74 77	FDD2-205		5.2 x 0.5	0.35	5.7	2.3	4.0	20.0		
74 51 94	FDD2-250		6.4 x 0.8	0.4	6.6	2.3	4.0	21.0		
73 75 09	FDD2-312		8.0 x 0.8	0.4	8.2	2.3	4.0	23.0		
73 75 54	FDD5.5-187	4~6mm ² 12~10 AWG	4.8 x 0.5	0.5	5.0	3.4	6.2	25.0	13.0	YELLOW
74 52 08	FDD5.5-250		6.4 x 0.8	0.4	6.6	3.4	6.2	25.0		
73 75 88	FDD5.5-312		8.0 x 0.8	0.5	8.2	3.4	6.2	25.0		