




PANDUIT PART NO. *	BUNDLE DIA.		A	B	C	D	E	F	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT4S	.06 (1.5)	4.00 (102)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	14.5 (368)	50 (222)	STANDARD	CURVED	.56 (254)
PLT4.5S	.06 (1.5)	4.50 (114)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	15.5 (394)	50 (222)	STANDARD	CURVED	.57 (257)
PLT5S	.06 (1.5)	5.00 (127)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	17.5 (445)	50 (222)	STANDARD	CURVED	.65 (293)
PLT6LH	.188 (4.8)	6.00 (152)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	21.9 (556)	120 (534)	LIGHT HEAVY	STRAIGHT	1.86 (845)
PLT7LH	.188 (4.8)	7.00 (178)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	24.7 (627)	120 (534)	LIGHT HEAVY	STRAIGHT	2.09 (950)
PLT8LH	.188 (4.8)	8.00 (203)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	27.6 (701)	120 (534)	LIGHT HEAVY	STRAIGHT	2.32 (1054)
PLT9LH	.188 (4.8)	9.00 (229)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	30.5 (775)	120 (534)	LIGHT HEAVY	STRAIGHT	2.56 (1161)
PLT10LH	.188 (4.8)	10.31 (262)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	34.3 (871)	120 (534)	LIGHT HEAVY	STRAIGHT	2.83 (1285)

NOTES:

- 1) RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.
- *2) SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, & PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

						TITLE PAN-TY CABLE TIES - PLT SERIES						
						CUSTOMER DRAWING						
						ITEM REVISION NAME W10001CC/26						
						DATASET FILE NAME W10001CC/26-SS-5540 SHEET 3 CUSTOMER						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .X = - - - .XXX = .020 (.51) .XX = .02 (.51) ANGLES = - - -						
						MATERIAL: NYLON 6.6						
						DRAWING NUMBER: SS-5540 SHEET 3						
26 8/13/13 BWG KJM RTFI UPDATED TITLE BORDER. SS-5540/26						THIRD ANGLE PROJECTION						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY CEW	DATE 12-27-84	CHK HVP	SCALE NONE	SHT 1 OF 1	SIZE A