

300 Series with Wera *slipSTOP*® Blade

The right screwdriver for any application.

367 TORX® Screwdriver



Application: For TORX® socket screws
Blade: Round, mat nickel

Tip: TORX®, Black Point
Handle: Kraftform® with anti-roll protection, three components

		A	B		A	
Code		mm	mm		inch	
028000	TX 5	60	70	3,5	2 3/8"	10
028001	TX 6	60	70	3,5	2 3/8"	10
028002	TX 7	60	70	3,5	2 3/8"	10
028003	TX 8	60	81	3,5	2 3/8"	10
028004	TX 9	60	81	4,0	2 3/8"	10
028005	TX 10	80	81	4,0	3 1/8"	10
028008	TX 15	80	98	4,0	3 1/8"	10
028010	TX 20	100	98	4,5	4"	10
028012	TX 25	100	105	5,0	4"	10
028013	TX 27	115	105	5,5	4 9/16"	10
028015	TX 30	115	105	6,0	4 9/16"	10
028020	TX 40	130	112	7,0	5 3/16"	10
028025	TX 45	130	112	8,0	5 3/16"	10

367 BO Resis-TORX® Screwdriver with bore-hole



Application: For Resis-TORX® (Tamper-resistant TORX®) socket screws
Blade: Round, mat nickel

Tip: TORX® BO, Black Point
Handle: Kraftform® with anti-roll protection, three components

		A	B		A	
Code		mm	mm		inch	
138257	TX 7	60	70	3,5	2 3/8"	5
138258	TX 8	60	81	3,5	2 3/8"	5
138259	TX 9	60	81	4,0	2 3/8"	5
138260	TX 10	80	81	4,0	3 1/8"	5
138261	TX 15	80	98	4,0	3 1/8"	5
138262	TX 20	100	98	4,5	4"	5
138263	TX 25	100	105	5,0	4"	5
138264	TX 27	115	105	5,5	4 9/16"	5
138265	TX 30	115	105	6,0	4 9/16"	5
138266	TX 40	130	112	7,0	5 3/16"	5

367 K Ballpoint-TORX® Screwdriver



Application: For TORX® socket screws
Blade: Round, mat nickel

Tip: TORX®-Ballpoint, Black Point
Handle: Kraftform® with anti-roll protection, three components

		A	B		A	
Code		mm	mm		inch	
027950	TX 15	80	98	4,0	3 1/8"	5
027952	TX 20	100	98	4,5	4"	5
027954	TX 25	100	105	5,0	4"	5
027956	TX 27	115	105	5,5	4 9/16"	5
027958	TX 30	115	105	6,0	4 9/16"	5
027960	TX 40	130	112	7,0	5 3/16"	5
027962	TX 45	130	112	8,0	5 3/16"	5

367 TORX PLUS® Screwdriver



Application: For TORX PLUS® socket screws
Blade: Round, mat nickel

Tip: TORX PLUS®, Black Point
Handle: Kraftform® with anti-roll protection, three components

		A	B		A	
Code		mm	mm		inch	
028029	5 IP	60	70	3,5	2 3/8"	5
028030	6 IP	60	70	3,5	2 3/8"	5
028031	7 IP	60	70	3,5	2 3/8"	5
028032	8 IP	60	70	3,5	2 3/8"	5
028033	9 IP	60	81	4,0	2 3/8"	5
028034	10 IP	80	81	4,0	3 1/8"	5
028035	15 IP	80	98	4,0	3 1/8"	5
028036	20 IP	100	98	4,5	4"	5
028037	25 IP	100	105	5,0	4"	5
028038	30 IP	115	105	6,0	4 9/16"	5