




Type	S3-B 3-pole, 1 connection level Coding ring optional Integrated retaining clip and labelling space
Rated current	10 A
Specifications	
Rated load	10 A / 250 V
Insulation	Test voltage V rms / 1 min
All terminals/DIN rail	2,5 kV
– Terminal/terminal	2,5 kV
Cross-section of connecting wire	
– Single-wire	4 mm ² or 2 x 2,5 mm ²
– Multi-wire	22 - 14 AWG
Max. screw torque	1,2 Nm
Screw dimensions	M3, Pozi, slot
Integrated retaining clip/plastic	for relay series C3
Labelling space	detachable
Connection label	1... 11; DIN/EN
Mounting	DIN rail T35 or mounting plate
Ambient temperature	-40 (no ice)...60 °C / -40 ... 80 °C
Associated, plug-in 11-pin MRC relays	C3-A, C3-G, C3-T, C3-X, C3-M, C3-R, C3-E, C3-N, C3-S
Suitable for holding the Releco coding ring	
For coding the relay and the socket.	
Accessories	
Coding ring, blue set:	S3-BC Packaging unit: 5 pcs
Retaining spring, steel	S3-C, S3-CT (with Timecube)



Connection diagram



Dimensions [mm]



Technical approvals, conformities



EN 60947-1, EN 61810-1

Type	S3-MP 3-pole, 1 connection level Integrated retaining clip and labelling space Accepts plug-in modules M3P in parallel with the coil
Rated current	10 A
Specifications	
Rated load	10 A / 250 V
Insulation	Test voltage V rms / 1 min
– All terminals/DIN rail	2,5 kV
– Terminal/terminal	2,5 kV
Cross-section of connecting wire	
– Single-wire	4 mm ² or 2 x 2,5 mm ²
– Multi-wire	22 - 14 AWG
Max. screw torque	1,2 Nm
Screw dimensions	M3, Pozí, slot
Integrated retaining clip/plastic	for relay series C3
Labelling space	detachable
Connection label	1...11; DIN/EN
Mounting	DIN rail T35 or mounting plate
Ambient temperature operation/storage	-40 (no ice)...60 °C / -40 ... 80 °C
Associated, plug-in 11-pin MRC relays	C3-A, C3-G, C3-T, C3-X, C3-M, C3-R, C3-E, C3-N, C3-S
Suitable for holding the Releco coding ring	
For coding the relay and the socket.	

Accessories



Coding ring, blue set:

Parallel module

Retaining spring, steel

S3-BC

Packaging unit: 5 pcs


M3P**S3-C, S3-CT** (with Timecube)**Connection diagram****Dimensions [mm]****M3P** Plug in modules for S3-MP

In parallel with the coil




Signaling LED

M3P-X / 24 Vac/dc
 M3P-X / 48 Vac/dc
 M3P-X / 110 ... 125 Vac/dc
 M3P-X / 200 ... 230 Vac/dc




Free wheeling diode and LED

M3P-DX / 24 Vdc
 M3P-DX / 48 Vdc
 M3P-DX / 110 ... 125 Vdc
 M3P-DX / 200 ... 230 Vdc




Free wheeling diode

M3P-DL / 12 ... 60 Vdc
 M3P-DH / 12 ... 250 Vdc

RC suppressor
(LED not available)

M3P-RC / 20 ... 50 Vac
 M3P-RC / 110 ... 120 Vac
 M3P-RC / 220 ... 240 Vac

**Technical approvals, conformities**

EN 60947-1, EN 61810-1