

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202320002](#)
Status: **Active**
Overview: [Brad M23 Signal and Power Connectors](#)
Description: Brad M23 Signal Connector, Straight Female Receptacle Housing Only, Cable Diameter 7.00-12.00mm

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Field Attachable / Accessories
Series	120232
Application	Signal
Comments	Housing Only
IP Rating	IP67
Material - Contact	N/A
Overview	Brad M23 Signal and Power Connectors
Product Name	Brad M23
Type	Field Attachable Connector
UPC	883906200947
Physical	
Cable Diameter	7.00-12.00mm (.276-.472")
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	None
Material - Connector Body	Nylon
Material - Coupling Nut	N/A
Material - Plating Mating	n/a
Net Weight	66.300/g
Orientation	Straight
Poles	N/A
Temperature Range - Operating	N/A
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	N/A
Voltage - Maximum	N/A
Material Info	
Engineering Number	KAS0S00-005
Reference - Drawing Numbers	
Sales Drawing	SD-120232-002



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant with Exemption 6(c) REACH SVHC Contained Per - D(2020)4578-DC (25 June 2020) Lead Halogen-Free Status Not Low-Halogen For more information, please visit Contact US	China RoHS
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[120232](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION