




Cordless Combi GSB 36 V-Li



Technical data

Torque, max. (hard screwdriving applications)	78 Nm
Torque setting range, min./max.	1 / 9 Nm
Torque, max. (soft screwdriving applications)	32 Nm
No-load speed (1st gear/2nd gear)	0 – 450 / 1.500 rpm
Max. impact rate	18.000 bpm
Chuck jaw width, min./max.	1,5 / 13 mm
Drill spindle thread	1/2"
Battery voltage	36 V
Battery capacity	1,3 Ah
Weight incl. battery	2,7 kg
Charging time, approx.	45 min
Torque settings	15+1
Length	280,0 mm
Width	95,0 mm
Height	271,0 mm

Cell type	Lithium-ions
Drilling diameter	
Max. drilling diameter in aluminium	16 mm
Max. drilling diameter in wood	50 mm
Max. drilling diameter in steel	16 mm
Max. drilling diameter in masonry	16 mm
Screw diameter	
Max. screw diameter	12 mm

Functions

- Multiple gears
- Self-drilling screws
- Impact drilling
- Forward/reverse operation
- Auto-Lock
- Softgrip

