



All rights strictly reserved. Reproduction or issue to third parties in any form
 whatsoever is not permitted without written authority from the proprietor.
 Property of F C I b.v.
 F C I b.v.



0.65 - 0.77 Hole Dia.

NOTES:

- 1 MATERIAL:
THERMOPL. POLYESTER 30% GLASS
FLAME RETARDANT ACC. UL 94-VO
COLOR NATURAL.
- 2 WHEN USING THIS PRODUCT IN A
STRAIGHT TO BOARD APPLICATION
THE FOLLOWING MUST BE TAKEN
INTO ACCOUNT:
 - 101LF HOUSING IS TO BE USED
FOR THE SOLDER TO BOARD
INSERT 88980-00ZLF.
 - 111LF HOUSING IS TO BE USED
FOR THE PRESS FIT TO BOARD
INSERT 88978-001LF.

3. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
4. THE HOUSING WILL WITHSTAND EXPOSURE TO 260 DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION. WITH A 1.6mm MINIMUM THICK CIRCUIT BOARD.

RECOMMENDED HOLE PATTERN
COMPONENT SIDE
FOR FEED THROUGH AND
SOLDER TO BOARD.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 ELECTRONICS www.fciconnect.com	
SEE NOTE 1									
ltr	ecn	no	date	linear angles  mm scale 5:1	D Andrews P Schalks D Coolmans	920424 920424 960119	title HEADER MINI COAX STRAIGHT 3x3 product family ETAL(tm) code 213 sheet 1 of 1		
A	H10346	DAN	920424						
B	H20755	DAN	921124						
C	H60040	RVI	960119						
D	H71012	RMA	970218						
E	H90476	DOB	990816	eng			product	family	code
F	P005-0436	CLW	051102	chr			size	dwg no	
sheet location		F 1		app			A2	88973	