


THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2005, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED VOLTAGE	24	Vdc
OPERATING VOLTAGE RANGE	10–28	Vdc
TONE OUTPUT	SEE 32 TONE CHART	–
RATED CURRENT	SEE 32 TONE CHART	mA
INGRESS PROTECTION	IP54	–
COLOR	WHITE	–
OPERATING TEMPERATURE	–25 ~ +70	°C
HOUSING MATERIAL	ABS	–
TERMINAL MATERIAL	SCREW	–
WEIGHT	150	grams

DETAIL "A"



1=CLOSED
0=OPEN

DETAIL "B"

VOLUME CONTROL





MAX

OPTIONAL COVER
AWA-05CWC

NOTES:


- ALL DIMENSIONS ARE IN MILLIMETERS.
- SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
- THIS PART IS RoHS 2002/95/EC COMPLIANT.

Ø113




REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
–	RELEASED FROM ENGINEERING	12/7/05	
A	ADDED RoHS & COVER NOTES	5/21/07	R.W.
B	REVISED DETAIL "A" DIL SWITCH	3/12/09	B.R.



DETAIL "A"

DETAIL "B"



UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN
MILLIMETERS, TOLERANCES ARE ±0.5 AND
ANGLES ARE ±3°.

APPROVALS	DATE
DRAWN J.A.F.	12/05
CHECKED E.P.	12/05
APPROVED B.R.	12/05

DO NOT SCALE DRAWING



projects®
unlimited

Dayton, Ohio

SIREN

SIZE
A

DRAWING NO.
AW-05CW-NC

SCALE: N.T.S.

SHEET 1 OF 1

FILE NAME
AW-05CW-NC.DWG