


RoHS Compliant

UC-049/ UC-072

LP uPCI 4xRS232 Opto Isolated TX RX

"SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"



Description

Universal PCI providing four low profile RS232 serial ports with Opto Isolation on TX RX lines (RTS and CTS lines are open circuit). Up to 921,600 data transfer rates and the 128 byte deep transmit and 128 byte receive FIFOs, coupled with 1Mbit/s line drivers deliver uncompromising performance on your PC. Includes drivers for all Windows 32 bit and 64 bit Operating Systems, including Windows 7.

With Brainboxes industry renowned Lifetime Warranty and Lifetime Support!

Features

- 4 port RS232
- PCI 3.0
- 128 Byte Tx and 128 Byte Rx FIFOs
- Up to 921,600 Baud
- DB9 connector (9 Pin Male)
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

Options



UC-049:
LP uPCI 4xRS232 Opto
Isolated TX RX

UC-072
uPCI 4xRS232 Opto
Isolated TX RX



Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows 7 32 bit & 64 bit Editions
- Windows Server 2008 32 bit & 64 bit Editions
- Windows Vista 32 bit & 64 bit editions
- Windows Server 2003 32 bit & 64 bit Editions



As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.




ORDER

Description

LP uPCI 4xRS232 Opto Isolated TX RX
uPCI 4xRS232 Opto Isolated TX RX

Code

UC-049
UC-072



LP uPCI 4xRS232 Opto Isolated TX RX

UC-049/ UC-072 Full Specification

Port 	Ports Connector FIFO size Operating Distance Cable	4 x RS232 Connector DB9 -- 9 Pin Male 128 RX FIFO + 128 TX FIFO EIA - RS232 Standard No Cable; Integrated Connector (UC-049) 4 port cable: 44 way D - 4x9 Pin (UC-072)
Port Settings 	Baud Rate Data Bits Parity Stop Bits Flow Control Tx/Rx Modes	921,600 5,6,7 or 8 Odd, Even, None, Mark or Space 1, 1.5 or 2 Point to Point
Interface 	OS Compatibility BUS	Microsoft Windows 7 32 bit & 64 bit Editions Windows Server 2008 32 bit & 64 bit Editions Windows Vista 32 bit & 64 bit Editions Windows Server 2003 32 bit & 64 bit Editions Windows XP 32 bit & 64 bit Editions Microsoft Windows 2000 DOS PCI : Universal PCI is fully compatible with both 3.3Volt and 5Volt PCI slots.
Approvals 	Industry Approvals Microsoft Approvals	Microsoft Certified Gold Partner WEEE RoHS EMC: CE TAA Windows 7 32 bit & 64 bit Editions Windows Server 2008 32 bit & 64 bit editions Windows Vista 32 bit & 64 bit editions Windows Server 2003 32 bit & 64 bit editions Windows XP 32 bit & 64 bit editions
General 	PCB Layers Power Consumption Weight Size	4 550mA @ 5V 0.072 kg (UC-049) 0.076 kg (UC-072)Kg null mm
Box Content	Packaging Card	Installation CD including manual, Microsoft signed drivers & utilities LP uPCI 4xRS232 Opto Isolated TX RX No Cable; Integrated Connector (UC-049) 4 port cable: 44 way D - 4x9 Pin (UC-072)
Product Support 	Warranty Support	Lifetime (online registration required) Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team
Additional 	OEM option Made In Customisable	Available for bulk buy OEM Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year" Brainboxes operate a "Perfect Fit Custom Design" policy for volume users. Serial Adapters, Ethernet Serial Adapters, PCI to Serial Adapters, ExpressCard Serial Adapter USB to Serial Adapters

Other PCI Cards: 1xRS232 | 2xRS232 | 4xRS232 | 8xRS232 | 1xRS422/485 | 2xRS422/485 | 4xRS422/485
Other Brainboxes Ranges: PCI Express | Bluetooth Serial Adapter | Ethernet Serial Adapter | PCI to Serial Adapter | ExpressCard Serial Adapter | USB to Serial Adapter