



2243L 22-inch Open-Frame Touchmonitor

selected **part numbers** discontinued August 2011;
suggested [replacement](#) offers analog and digital video inputs



The Elo TouchSystems 2243L open-frame LCD touchmonitor with its slim design and narrow outside dimensions gives kiosk integrators an edge in developing the most aesthetically pleasing products. Wide-aspect displays like the Elo 2243L are easier to use and incorporate than traditional open-frame touchmonitors. Wide-screen format displays allow extra content on the screen and are quickly becoming preferred in casino gaming, amusement and entertainment settings and are increasingly popular in public venue environments due to the high-definition cinematic-like experience. Typical applications for the 2243L include: gaming and amusement, information kiosks and self-service, as well as interactive digital signage applications.

State-of-the-art LED backlighting used in the 2243L makes the panel thinner overall as the cold cathode fluorescent lights (CCFL) are replaced with LED lights. LED lights also take less electricity to operate and generate less heat. This leads to the slimmer dimensions of the 2243L that facilitate OEMs and system integrators the flexibility to design aesthetically pleasing and stylish kiosks.

Available with either IntelliTouch surface acoustic wave touchscreen technology or Acoustic Pulse Recognition (APR), the 2243L provides stable "drift-free" operation with outstanding image clarity, resolution, and light transmission - for an accurate touch response and vivid images. APR is the recent TE innovation that supports touch activation by any stylus - pen, glove, bare finger and fingernail, while IntelliTouch is the optical standard of touch and widely used in kiosk and gaming applications. Both are pure glass construction to deliver a clear, bright and long-lasting performance and it also makes the touchscreens scratch-resistant. It is nearly impossible to physically "wear out" these touchscreens.

[Press release](#) • [Compare Elo touchmonitors](#).

Features	Specifications	Accessories	Part Numbers	Support
----------	----------------	-------------	--------------	---------

How-to-Buy

Technology ?	Interface ?	Input Video Format	Surface Treatment	Part # (RoHS Compliant)	Availability
No Touch	USB	VGA	Clear	E918918	Worldwide
No Touch	USB	DVI/Analog VGA	Clear	E350335	Worldwide
IntelliTouch	USB	VGA	Clear	E932814	Worldwide
IntelliTouch	USB	DVI/Analog VGA	Clear	E059181	Worldwide
APR	USB	VGA	Antiglare	E236501	Worldwide
APR	USB	DVI/Analog VGA	Antiglare	E304159	Worldwide

* SecureTouch monitors use a 3 mm chemically strengthened glass touch sensor.

Power Brick and Cable Kit: 12V, 4.16A, 50W (sold separately)

Part #	Region	Product Description
E348315	N. America	North America power brick
E162361	EMEA	European power brick
E334749	U.K. & Korea	UK & Korea power brick
E834397	Asia	China power brick
E953228	Asia	Taiwan power brick
E033396	Asia	Japan power brick
E707702	Argentina	Argentina power brick

[Contact Us](#)
[Careers at Elo](#)
[Languages](#)
[Site Map](#)
[Newsletter](#)

[Warranty Policies](#)
[Locate a reseller](#)
[Find Documents & Drawings](#)

© Elo Touch Solutions, Inc. All rights reserved. | [Privacy Policy](#)