

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [130102-0183](#)  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Super-Safeway™ Rubber Hand Lamp with 100W Open End Reflector Guard with Switch and Receptacle 7.62m (25.0') 16/3 SOOW, Vinyl Guard

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

**Agency Certification**

CSA LR85374

**General**

Product Family Portable Lighting  
Series [130102](#)  
NEMA Configuration NEMA 5-15  
Outlet Side  
Overview [Hand Lamps](#)  
Product Literature Order No 987650-8053  
Product Name Super-Safeway™  
Type Hand Lamps  
UPC 78678860405  
Woodhead Yes

**Physical**

Cord Length - Primary 7.62m (25.0')  
Cord Length - Secondary N/A  
Depth 153.92mm (6.060")  
Duty Industrial  
Guard Included No  
Guard Type Metal Wire  
Height 311.66mm (12.270")  
Length N/A  
Material - Guard #8 Gauge Zinc-plated Steel  
Mounting Style Hand Held  
Net Weight 204.110/kg  
Packaging Type Carton  
Socket Construction N/A

**Electrical**

Bulb Type Incandescent  
Cord Type - Primary 16/3 SOOW  
Lamp Type A21  
Lamp Wattage - Maximum 100W  
Lumens 1000  
On/Off Switch Yes  
Voltage (Fixture) - Maximum 240V

**Material Info**

Old Part Number 114USIA163



image - Reference only

Series

**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

**Not Reviewed**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of  
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
non-product compliance questions.

**Search Parts in this Series**

[130102Series](#)