

MINI-BAT/12DC/2.6AH

Order No.: 2866569



<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=2866569>

Rechargeable battery module, lead AGM, VRLA technology, 12 V DC, 2.6 Ah.

Commercial data

EAN	4 046356 476485
Pack	1
Customs tariff	85072080
Country of Origin	CN
Catalog page information	Page 623 (IF-2011)

Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Input data

Nominal input voltage	12 V DC
Current consumption	1 A (charging process)
Buffer period	(See the selection diagram)

Output data

Nominal output voltage	12 V DC
Output current	max. 15 A
Connection in series	No
Output fuse	25 A

General data

IQ technology	No
Disposal	Used batteries must not be thrown away with household waste, they should instead be disposed of in accordance with applicable national regulations. They can also be returned to Phoenix Contact or the manufacturer.
Width	52 mm
Height	130 mm
Depth	110 mm
Net weight	1.7 kg
Degree of protection	IP20
Protection class	III
Ambient temperature (operation)	0 °C ... 40 °C
Ambient temperature (storage/transport)	0 °C ... 40 °C

Certificates

Certifications applied for: UL-EX LIS

Accessories

Item	Designation	Description
Fuse		
0913757	SI FORM C 25 A DIN 72581	Flat-type plug-in fuse, type C, color code: white, nominal current: 25 A

General

2938196	QUINT-PS-ADAPTERS7/1	Assembly adapter for QUINT-PS... power supply on S7-300 rail
2853983	UTA 107	Universal DIN rail adapter, for screwing on switchgear
2938235	UWA 182/52	Universal wall adapter

Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG, England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;