



Ring Tongues – Vinyl Insulated Butted Seam 16-14 AWG




| Product Number† | UPC (054007-) | Wire Range (AWG) | Stud Size | W    | C    | L    | E    | Thickness | Barrel Length | Barrel I.D. | Maximum Insulation Diameter | Terminals per Case |
|-----------------|---------------|------------------|-----------|------|------|------|------|-----------|---------------|-------------|-----------------------------|--------------------|
| MVU14-4R/SK     | 01444         | 16-14            | 4         | 0.25 | 0.22 | 0.80 | 0.67 | 0.030     | 0.25          | 0.090       | 0.170                       | 1000               |
| MVU14-6R/SK     | 01446         | 16-14            | 6         | 0.25 | 0.22 | 0.80 | 0.67 | 0.030     | 0.25          | 0.090       | 0.170                       | 1000               |
| MVU14-8R/SK     | 01449         | 16-14            | 8         | 0.25 | 0.22 | 0.80 | 0.67 | 0.030     | 0.25          | 0.090       | 0.170                       | 1000               |
| MVU14-8RK       | 01450         | 16-14            | 8         | 0.33 | 0.29 | 0.90 | 0.74 | 0.030     | 0.25          | 0.090       | 0.170                       | 1000               |
| MVU14-8R/LK     | 01451         | 16-14            | 8         | 0.31 | 0.33 | 0.93 | 0.78 | 0.030     | 0.25          | 0.090       | 0.170                       | 1000               |
| MVU14-10RK      | 01452         | 16-14            | 10        | 0.33 | 0.29 | 0.90 | 0.74 | 0.030     | 0.25          | 0.090       | 0.170                       | 1000               |
| MVU14-10R/LK    | 01453         | 16-14            | 10        | 0.31 | 0.33 | 0.93 | 0.78 | 0.030     | 0.25          | 0.090       | 0.170                       | 1000               |
| MVU14-14R/SK    | 01454         | 16-14            | 1/4       | 0.47 | 0.40 | 1.08 | 0.85 | 0.030     | 0.25          | 0.090       | 0.170                       | 1000               |
| MVU14-516R/SK   | 01456         | 16-14            | 5/16      | 0.47 | 0.40 | 1.08 | 0.85 | 0.030     | 0.25          | 0.090       | 0.170                       | 1000               |
| MVU14-38RK      | 01458         | 16-14            | 3/8       | 0.56 | 0.40 | 1.13 | 0.85 | 0.030     | 0.25          | 0.090       | 0.170                       | 1000               |




MVU14-4R/S  
Stud Size 4  
Wire Range 16-14




MVU14-6R/S  
Stud Size 6  
Wire Range 16-14




MVU14-8R/S  
Stud Size 8  
Wire Range 16-14




MVU14-8R  
Stud Size 8  
Wire Range 16-14




MVU14-8R/L  
Stud Size 8  
Wire Range 16-14




MVU14-10R  
Stud Size 10  
Wire Range 16-14




MVU14-10R/L  
Stud Size 10  
Wire Range 16-14



MVU14-14R/S  
Stud Size 1/4  
Wire Range 16-14



MVU14-516R/S  
Stud Size 5/16  
Wire Range 16-14



MVU14-38R  
Stud Size 3/8  
Wire Range 16-14