


NUMBER 917389








METRIC

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST

AMP-J
REV.10/83



NOTES

- MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, UL94V-0
CONTACT: COPPER ALLOY
RETENTION LEG: COPPER ALLOY
- FINISH (CONTACT AREA): 0.38 μm MIN GOLD PLATING OVER NI PLATING
- FINISH (CONTACT AREA): 0.76 μm MIN GOLD PLATING OVER NI PLATING
- FINISH (RETENTION LEG): TIN PLATED (SOLDER TYING) OVER NICKEL

注記

- 材料: ハウジング: ガラス入り熱可塑性樹脂, UL94V-0
コンタクト: 銅合金
リテンションレグ: 銅合金
- めっき: コンタクト接触部: ニッケル下地の上に金めっき 0.38 μm MIN
- めっき: コンタクト接触部: ニッケル下地の上に金めっき 0.76 μm MIN
- めっき: リテンションレグとコンタクト半田付部: ニッケル下地の上にスズめっき

Y	4	3	2-917389-3
Y	4	2	2-917389-2
X	4	3	1-917389-3
X	4	2	1-917389-2
キー (KEY)	(FINISH)		製品番号 (PART NO.)

A	REVISED (FJD0-0039-03)	TSM	12/19/94
0	RELEASED (FJ00-1419-94)	KI	S.M.
LTR	REVISION RECORD	DR	CHK DATE

Copyright © 1994 AMP (Japan) LTD. ALL RIGHTS RESERVED.		tyco Electronics		Tyco Electronics AMP K.K. Kawasaki, Japan	
WIRE RANGE mm² (AWG -)		INSULATION DIA mmφ		NAME ダイナミック D3200 H-ヘッダーアセンブリー 3 極 表面実装 タイプ 3 POS SINGLE ROW SMT TYPE HORIZONTAL HDR ASS'Y FOR DYNAMIC 3200	
MATERIAL SEE NOTE 注記参照		FINISH SEE NOTE 注記参照		一般公差 (GENERAL TOLERANCE) 10mm以下: ±0.3 10mm以上30mm以下: ±0.4 30mm以上100mm以下: ±0.45 角度: ±3°	
DR. K.IKEDA 16/DEC/94		DE. K.IKEDA 16/DEC/94		SIZE A3	
CHK. S.MANABE 19 DEC 94		APP. S.MANABE 19 DEC 94		SCALE 2-1	
				REV. A	
				SHEET 1 OF 1	

(CUSTOMER DRAWING) 顧客用図面

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-917389-2](#)