



Sample photo

Order symbol: ABS 200/100 XHT
Product nbr: 6083926
Description: Enclosure, ABS
Remarks: Smoked transparent cover

EAN: 6418074021724
El. number:
Finland: 3421742
Denmark: 8212023864
Italy: 7362145
Norway:

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		255	180	100	Ingress Protection (EN 60529): IP 66/67
inch:		10.0	7.1	3.9	Impact Resistance (EN 62262): IK 07
Materials:					Electrical insulation: Totally insulated
Material:		ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:		Smoked grey			Glow Wire Test (IEC 695-2-1) °C: 650
Cover screws material:		Polyamide			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
Cover screws colour:		Black			Certificates:
Gasket material:		Polyurethane			
Temperatures:					Fimko
Short term:		-40 ... 80 °C			Europe EN 62208: 2003
Continuous:		-40 ... 60 °C			Gost R
Short term:		-40 ... 175 °F			
Continuous:		-40 ... 140 °F			
Accessories:					
MIV 200		Mounting plate (Galvanized steel)			
MIN 15		DIN-15 Mounting rail			
MIN 20		DIN-15 Mounting rail			
MIV 15		DIN-35 Mounting rail			
MIV 20		DIN-35 Mounting rail			
FP A 200/180		Front plate (Aluminium)			
HFP 180		Front plate hinge series (2 pcs)			
FP 22046		Wall fastening lug (4 pcs)			

