

CABLE BREAKOUT BOOTS, THREE ENTRY




Table of Dimensions, inch (mm):

PART NUMBER (See Note*)	BODY ID		LEG ID		Length Recovered		Rec'd. Wall Thickness Ref (W)
	Exp. (A), Min	Rec'd. (B), Max	Exp. (C), Min	Rec'd. (D), Max	Min (E), Body	(F), Leg	
T3-9FR	0.90 (23)	0.36 (9)	0.33 (8)	0.12 (3)	2.0 (51)	0.7 (18)	0.04 (1.0)
T14-23FR	1.20 (30)	0.69 (18)	0.50 (13)	0.18 (5)	2.3 (58)	1.0 (25)	0.09 (2.3)
T23-50FR	1.20 (30)	0.69 (18)	0.50 (13)	0.18 (5)	2.3 (58)	1.0 (25)	0.09 (2.3)
T42-100FR	1.70 (43)	0.90 (23)	0.82 (21)	0.30 (8)	2.3 (58)	1.2 (30)	0.12 (3.0)
T60-150FR	1.70 (43)	0.90 (23)	0.82 (21)	0.30 (8)	2.3 (58)	1.2 (30)	0.12 (3.0)
T150-300FR	2.40 (61)	1.40 (36)	1.25 (32)	0.50 (13)	3.5 (89)	1.6 (41)	0.12 (3.0)
T200-400FR	2.40 (61)	1.40 (36)	1.25 (32)	0.50 (13)	3.5 (89)	1.6 (41)	0.12 (3.0)
T-400FR	3.20 (81)	2.00 (51)	1.40 (36)	0.75 (19)	3.5 (89)	1.6 (41)	0.14 (3.6)
T500-600FR	4.90 (124)	2.32 (59)	2.00 (51)	1.00 (25)	7.5 (191)	2.2 (56)	0.12 (3.0)

Note*: Add "NA" to the end of Part Number if no adhesive is required

Material: Heat shrinkable boot material in accordance with –3 polyolefin

Factory applied sealant: Factory applied hot melt adhesive is standard.

CUSTOMER DRAWING

		Raychem Molded Parts 305 Constitution Drive, Menlo Park, CA 94025		TITLE: CABLE BREAKOUT BOOT, THREE ENTRY		
Unless otherwise specified dimensions are in inches. [Metric dimensions are shown in brackets]				DOCUMENT NO.: TXXX-XXXFR		
Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.				REV: G		
				SCALE: None		DATE: August 27, 2009
REVISED BY: <i>UNGUYEN</i>	CAGE CODE: 06090	Org. Date: 5/7/07	ECO #: 09-019755	FILE : TXXX-XXXFR.doc	SIZE A	SHEET: 1 of 1

© 2003-2009 Tyco Electronics Corporation. All rights reserved

If this document is printed it becomes uncontrolled. Check for the latest revision.