


PAC

PTFE TYPE A Cable (20 AWG) Specification

19/0.20 SPC

Part No.:PTFE20A100

Cross Section		Performance	
 Conductor Jacket		Electrical Characteristics: Spark Test: AC-1.5KV Dielectric Strength : AC-300V/60sec Conductor Resistance: 37 OHM/KM At 20°C Insulation Resistance: DC-500V 10 Mohm/KM At 20°C	
Packing			
As request			
Description			
Rated Temperature (°C)	-75~190		
Rated Voltage(V)	300		
Product Standard Certification			
Flammability Test	FT1		
Construction			
Conductor	Silver plated copper		
AWG	20		
Conductor Dia. (±0.005mm)	19/0.20		
Jacket	PTFE		
Average Thickness(mm)	0.13		
Outer Dia.(±0.05mm)	1.30		
Color		Mechanical Characteristics:	
As request			
Marking			
PAC 20AWG 300V 190°C			
Revision History			