


PL-24-A

AC COUPLED SURFACE MOUNT HIGH IP3 MIXER



SPECIFICATIONS

Name:	PL-24-A
Frequency Range:	
RF:	1-3500 MHz
LO:	1-3500 MHz
IF:	1-2000 MHz
LO Power:	+10 dBm
Conversion Loss:	8.5 dB max.
1 dB Compression Point:	+5 dBm typ.
IP3:	
Typ:	+15 dBm
Min:	+12 dBm
Isolation:	
LO/RF:	25 dB min.
LO/IF:	20 dB min.
Package Type:	Surface

Also available in outlines 411 & 414.

PORT CONFIGURATION

RF:	1
LO:	3
IF:	2
Ground:	All Others

This is a commercial off the shelf (COTS) product.
For an equivalent product that meets DFARS materials compliance, contact sales.
All specifications are subject to change without notice at any time. Rev: 190326