




SILENCER (1, 2, 4), EXHAUST PROTECTOR (3)

		catalogue number			
		(1)	(2)	(3)	(4)
operating pressure		0 to 10 bar		0 to 12 bar	0 to 13,8 bar
ambient temperature		-10°C to +80°C			-20°C to +110°C
construction	body	porous plastic	porous bronze	bronze	zinc-plated steel, bichromate
	connection piece	plastic	brass	brass	
	diffuser	-	-	-	
pipe size	Ø M5	34600405	34600207	34600491	-
	G 1/8	34600406	34600001	34600492	34600485
	G 1/4	34600407	34600002	34600493	34600486
	G 3/8	34600408	34600003	34600494	34600487
	G 1/2	34600409	34600004	34600495	34600488
	G 3/4	34600410	34600005	34600496	34600489
	G 1	34600411	34600006	34600497	34600490



SHUTTLE VALVE

Fluid Air or filtered neutral gas, lubricated or not
Operating pressure 1 to 10 bar
Ambient temperature -10°C to +60°C
CONSTRUCTION
Body Black anodised aluminium
Internal parts Steel + NBR (nitrile)


		
pipe size	Ø orifice (mm)	catalogue number
G 1/8	3,2	34600127
G 1/4	6	34600119



NON-RETURN VALVE


Fluid Air or filtered neutral gas, lubricated or not
Operating pressure
 plastic body 1 to 10 bar
 metal body 0,5 to 10 bar
Ambient temperature -10°C to +60°C
CONSTRUCTION
Body
 instant fittings version Technical polymer
 tapped version Brass nickle
Internal parts Light alloy and brass
Seals NBR (nitrile)

		
pipe size	flow at 6 bar (l/min)	catalogue number
(5) plastic body (instant fittings)		
Ø 4 mm ext.	330	34602445
Ø 6 mm ext.	665	34602446
Ø 8 mm ext.	1630	34602447
(6) metal body (tapped)		
Ø M5	190	34602412
G 1/8	920	34602124
G 1/4	1650	34602125
G 3/8	2400	34602444
G 1/2	3500	34602126



QUICK EXHAUST VALVE


Fluid Air or filtered neutral gas, lubricated or not
Operating pressure 0,5 to 10 bar
Ambient temperature -10°C to +60°C
CONSTRUCTION
Body Light alloy
Membran NBR (nitrile)

		
pipe size	Ø orifice (mm)	catalogue number
G 1/4	12	34600136
G 3/8	12	34600137
G 1/2	20	34600138
G 3/4	20	34600139



PNEUMATIC INDICATOR


Fluid Air or filtered neutral gas, lubricated or not
Operating pressure 2 to 8 bar
Ambient temperature +5°C to +70°C
Angle of vision 180°
CONSTRUCTION
Lens PC (polycarbonate)
Body and collar POM (polyacetal)
Nut Brass

	
color	catalogue number
red	34600130
green	34600131
yellow	34600132



DIMENSIONS (mm), WEIGHT (kg)

SILENCER, EXHAUST PROTECTOR



(1)					
cat. number	ØA	B	C	ØD	weight
34600405	M5	16	5	7	0,0005
34600406	G1/8	27	6	13	0,002
34600407	G1/4	34	7	15	0,004
34600408	G3/8	55	11	18	0,006
34600409	G1/2	62	12	23	0,010
34600410	G3/4	113	16	38	0,040
34600411	G1	141	20	48	0,065


(2)					
cat. number	ØA	B	C	D	weight
34600207	M5	18	4	8	0,004
34600001	G1/8*	22,4	5,6	13	0,010
34600002	G1/4*	41,6	8,4	16	0,030
34600003	G3/8*	49,2	8,8	24	0,030
34600004	G1/2*	54,6	11,4	27	0,070
34600005	G3/4*	82,3	12,7	36	0,300
34600006	G1*	93,5	14,5	50	0,400

(3)					
cat. number	ØA	B	C	D	weight
34600491	M5	4,5	3,5	8	0,002
34600492	G1/8	10	6	13	0,007
34600493	G1/4	11	8	16	0,011
34600494	G3/8	12	9	19	0,016
34600495	G1/2	12	11	24	0,027
34600496	G3/4	14	13	30	0,044
34600497	G1	14	15	36	0,065

(4)					
cat. number	ØA	B	C	D	weight
-	-	-	-	-	-
34600485	G1/8*	31	4	11,1	0,009
34600486	G1/4*	39	5,6	14,3	0,023
34600487	G3/8*	51	6,4	17,5	0,036
34600488	G1/2*	61	8	22,2	0,068
34600489	G3/4*	72	8,8	27	0,136
34600490	G1*	88	10,3	33,3	0,227


* taper

SHUTTLE VALVE




cat. number	ØA	B	C	D	E	F	H	I	J	weight
34600127	G1/8	26	16	8,5	51	20,5	32	9,5	4,5	0,150
34600119	G1/4	30	20	10,5	52	21,5	35	8,5	5,5	0,210

NON-RETURN VALVE




cat. number	ØA	B	C	ØD	weight
(5) plastic body (instant fittings)					
34602445	Ø 4 mm ext.	38	-	16	0,008
34602446	Ø 6 mm ext.	41	-	16	0,013
34602447	Ø 8 mm ext.	51,5	-	19	0,018
(6) metal body (tapped)					
34602412	Ø M5	25	8	-	0,008
34602124	G 1/8	36,5	13	-	0,025
34602125	G 1/4	41	16	-	0,041
34602444	G 3/8	51	20	-	0,074
34602126	G 1/2	62	24	-	0,120

QUICK-EXHAUST VALVE



cat. number	ØA	B	C	D	E	F	weight
34600136	G1/4	64	52	13	25	64	0,185
34600137	G3/8	64	52	13	25	64	0,185
34600138	G1/2	85	72	19	38	97	0,420
34600139	G3/4	85	72	19	38	97	0,390

PNEUMATIC INDICATOR
weight : 0,035 kg



- ① Angle of vision 180°
- ② Instant fittings for flexible tube Ø 4 O.D