

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TWIST TIES




FIGURE 1

T568B WIRING SCHEME

PLUG POSITION:

1
2
3
4
5
6
7
8

CABLE WIRE:
WHITE/ORANGE
ORANGE
WHITE/GREEN
BLUE
WHITE/BLUE
GREEN
WHITE/BROWN
BROWN

NOTES:

1. TX6A-SD 10GIG UTP PLUG-TO-PLUG ZONE CORD
2. 100% PERFORMANCE TESTED TO CATEGORY 6A PERMANENT LINK LIMITS.
3. TERMINATED WITH (8 POSITION) RJ45 MODULAR PLUGS AT BOTH ENDS PER T568B
4. CONSTRUCTED WITH 26AWG SOLID CATEGORY 6A UTP RISER, PLENUM, AND LOW SMOKE ZERO HALOGEN CABLE
5. MATERIALS:
PLUG: POLYCARBONATE
BOOT: CLEAR PVC




FIGURE 2

SEE SHEET 2 FOR ZONE CORD
LENGTHS AND PART NUMBERS

PART NUMBER		PRODUCT SPEC/PKG SPEC	
UXP* SERIES		N/A	
I.I. NUMBER		WORK INSTRUCTION	
N/A		N/A	
TITLE			
TX6A-SD 10GIG UTP PLUG-TO-PLUG ZONE CORD			
CUSTOMER DRAWING			
ITEM REVISION NAME		PANDUIT	
09M129BG/01			
DATASET FILE NAME		MATERIAL:	
09M129BG-DC02/01A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		DRAWING NUMBER: 09M129BG-02	
.x ± .06 [1.5] .xxx ± .010 [.3] .xx ± ANGLES ±			
THIRD ANGLE PROJECTION			
DRAWN BY	DATE	CHK	SCALE
BJN	3-22-10	KSM	NONE
SHT 1 OF 2			SIZE
			A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


10GIG SD UTP PLUG-TO-PLUG ZONE CORDS

PART NUMBERS	PART NUMBERS
UXPPBU** (PLENUM) UXPRBU** (RISER)	UXPLWH**M (LSZH)
MIN. CABLE LENGTH	MIN. CABLE LENGTH
10 FT (120")	4 METERS (158")
15 FT (180")	5 METERS (197")
20 FT (240")	6 METERS (237")
25 FT (300")	7 METERS (276")
30 FT (360")	8 METERS (315")
35 FT (420")	9 METERS (355")
40 FT (480")	10 METERS (394")
45 FT (540")	11 METERS (434")
50 FT (600")	12 METERS (473")
55 FT (660")	13 METERS (512")
60 FT (720")	14 METERS (552")
65 FT (780")	15 METERS (591")
70 FT (840")	16 METERS (630")
75 FT (900")	18 METERS (709")
80 FT (960")	20 METERS (788")
85 FT (1020")	22 METERS (867")
90 FT (1080")	24 METERS (945")
95 FT (1140")	25 METERS (985")
100 FT (1200")	26 METERS (1024")
110 FT (1320")	28 METERS (1103")
120 FT (1440")	30 METERS (1182")
130 FT (1560")	32 METERS (1260")
140 FT (1680")	34 METERS (1339")
150 FT (1800")	36 METERS (1418")
	38 METERS (1497")
	40 METERS (1575")
	42 METERS (1654")
	44 METERS (1733")
	46 METERS (1812")
	48 METERS (1890")
	50 METERS (1969")

PLENUM, AND RISER OFFERED WITH BLUE CABLE. (FEET ONLY)
LSZH OFFERED WITH WHITE CABLE. (METERS ONLY)

STRAIN RELIEF BOOTS AVAILABLE IN CLEAR ONLY.

**=LENGTH (SEE FIGURE 2, SHEET 1)

PART NUMBER		PRODUCT SPEC/PKG SPEC	
UXP* SERIES		N/A	
I.I. NUMBER		WORK INSTRUCTION	
N/A		N/A	
TITLE			
TX6 10GIG UTP -PLUG-TO-PLUG SD ZONE CORD			
CUSTOMER DRAWING			
ITEM REVISION NAME		PANDUIT	
09M129BG/01			
DATASET FILE NAME			
09M129BG-DC02/01A		MATERIAL:	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		DRAWING NUMBER:	
.x ± .06 [1.5] .xxx ± .010 [.3] .xx ± ANGLES ±		09M129BG-02	
		THIRD ANGLE PROJECTION	
DRAWN BY	DATE	CHK	SCALE
BJN	3-22-10	KSM	NONE
REV		SHT 2 OF 2	
DATE		A	
BY	CHK		
APR	DESCRIPTION		
ECN			