

**Part Number: 85548-0025**

Modular Jack, Right Angle, HyperJack™, Stacked, 12 Ports

Image not available

Status:	OBSOLETE
Replacement:	Contact Molex
Series:	85548
Category:	Modular Jacks/Plugs
Overview:	Magnetic Modular Jacks

Series image - Reference only

Mates With Part(s):

FCC 68 Plugs

Product Environmental Compliance

[EU RoHS](#): Compliance Status Not Reviewed
[China RoHS](#):
[REACH SVHC](#): Not Reviewed
[Low-Halogen Status](#): Not Reviewed

Part Detail**General**

Status	Obsolete
Category	Modular Jacks/Plugs
Series	85548
Component Type	PCB Jack
Magnetic	No
Obsolete Date	2003/09/01
Overview	Magnetic Modular Jacks
Performance Category	N/A
Power over Ethernet (PoE)	N/A
Product Name	HyperJack™

Physical

Durability (mating cycles max)	750
Flammability	94V-0
Inverted / Top Latch	No, Yes
Lightpipes/LEDs	None
Orientation	Right Angle (Side Entry)
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Ports	12
Positions / Loaded Contacts	8/8
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	0°C to +70°C
Termination Interface: Style	Through Hole
Wire/Cable Type	N/A

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	1.5A
Shielded	Yes
Voltage - Maximum	125V

Agency Certification

UL	E107635
----	---------

Material Info

UPC	800756028033
-----	--------------

Reference - Drawing Numbers

Product Specification	PS-85548-044
Sales Drawing	SD-85548-006

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then

contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)