

CONDUCTIVE BOXES + SMD-BOXES

CONDUCTIVE SUITCASES AND INSERTS



Art. No.	K 2012 ESD	K 2005 ESD	K 2001 ESD	K 2004 ESD	K 2006 ESD	K 2000 ESD	K 2007 ESD	K 2011 ESD
Inside dimensions	120 x 80 x 24	170 x 130 x 37	240 x 170 x 42	270 x 185 x 76	335 x 240 x 71	340 x 250 x 53	365 x 245 x 105	375 x 265 x 80

VACUUM FORMED INSERTS Please specify art. no. separately!



gridded foam

napped-foam

foam-fit

TE = vacuum formed insert

Overview conductive inserts for cases

Suitcases	K 2012 ESD	K 2005 ESD	K 2001 ESD	K 2004 ESD	K 2006 ESD	K 2000 ESD	K 2007 ESD	K 2011 ESD
Inside dimension (mm)	120 x 80 x 24	170 x 130 x 37	240 x 170 x 42	270 x 185 x 76	335 x 240 x 71	340 x 250 x 53	365 x 245 x 105	375 x 265 x 80
Conductive case inserts								
N/S:								
Napped foam	K 2012 ESD Noppe	K 2005 ESD Noppe	K 2001 ESD Steck	K 2004 ESD Noppe	K 2006 ESD Noppe	K 2000 ESD Noppe	K 2007 ESD Noppe	K 2011 ESD Noppe
	Cutting pattern / Stud	Cutting pattern / Stud	Foam fit for insertion / Stud	Stud / Stud	Stud / Stud	Stud / Stud	Stud / Stud	Stud / Stud
R:								
Gridded foam	no	no	K 2001 ESD Raster	K 2004 ESD Raster	K 2006 ESD Raster	K 2000 ESD Raster	K 2007 ESD Raster	K 2011 ESD Raster
Grid in mm	no	no	10 x 10 x 17 mm	10 x 10 x 30 mm	10 x 10 x 30 mm	12 x 12 x 20 mm	15 x 15 x 70 mm	12 x 12 x 20 mm
TE:								
TE 4	TE 4 K 12-6-10	no	no	no	TE 6 K 6-6-10	no	no	no
compartment TE 4	53 x 38 mm	no	no	no	149 x 104 mm	no	no	no
TE 6	TE 6 K12-6-10	TE 6 K5-6-10	TE 6 K1-6-10	TE 6 K4-6-10	no	TE 6 K-6-10	no	TE 6 K11-6-10
compartment TE 6	38 x 35 mm	56 x 50 mm	77 x 72 mm	81 x 78 mm	no	157 x 71 mm	no	168 x 71 mm
TE 8	no	no	no	no	TE 8 K6-6-10	nein	no	no
compartment TE 8	no	no	no	no	140 x 70 mm	nein	no	no
TE 9	no	TE 9 K5-6-10	TE 9 K1-6-10	TE 9 K4-6-10	no	TE 9 K-6-10	no	TE 9 K11-6-10
compartment TE 9	no	50 x 36 mm	72 x 50 mm	81 x 50 mm	no	102 x 71 mm	no	108 x 71 mm
TE 12	TE 12 K12-6-10	no	TE 12 K1-6-10	no	no	TE 12 K-6-10	no	TE 12 K11-6-10
compartment TE 12	25 x 24 mm	no	53 x 50 mm	no	no	102 x 71 mm	no	102 x 71 mm
TE 12						TE 24 K-6-10		
compartment TE 24						50 x 47 mm		