




[Home](#) [About Us](#) ■ [Products](#) ■ [Applications](#) ■ [Sales Support](#) ■ [Contact Us](#)



[Industrial Products](#) > [Connectors](#) > [Harsh Environment Connectors](#) > [Mega-Con-X Connectors 1.27" OD](#) > [Mega-Con-X Panel Connector](#)



[enlarge](#)

Mega-Con-X Panel Connector

Utilizing a separate o-ring, Mega Con X connectors are available up to 31-#20 pins/sockets. Can be ordered with quick connect type or threaded type coupling. Meets NEMA 6P when mated.

[Part Builder](#) [Specifications](#) [Downloads](#)

Need more info? Contact Conxall customer service

Series: **Mega-Con-X**

Connector Type: Cable End Panel Mount

Contact Size: #20

Contact Style: P/C Tail 0.187" (4.7)(Supplied assembled)

Number of Pins/ Contacts: 31 [contact arrangement](#)

Type of Contact: Pin Socket

Contact Plating: Gold over Nickel (standard)

Coupling Type: Twist Lock Threaded

Backshell Style: Panel mount with hex nut and gasket

Your Part Number: **24281-31SG-300**

Description: Mega-Con-X 31-position Panel Mount connector; #20 gold plated P/C tail .187 style Sockets; Twist Lock coupling; standard panel mount backshell

Drawings:  [In stock at 2 distributor\(s\).](#)

Availability:  [In stock at 2 distributor\(s\).](#)

Notes: P/C Tail contacts are only available on panel style connectors.

Consult factory for custom design cable assemblies and connectors.

5555 N Elston Ave • Chicago • Illinois • 60630 • USA • 1.773.792.2700

Home About Us Sales Contact Us Login

We are a **HEICO**® Company

Switchcraft®
USA

conxall®

Switchcraft®
KOREA