



# SUHNER® COAXIAL CONNECTOR DATA SHEET

## TYPE 24\_MCX-50-2-3/111\_N

### Description

Straight panel bulkhead cable jack, flange mount

### Front mount chassis connector



### General Information

MCX Interface dims acc. to:  
Weight:

IEC 60169-36\_CECC 22220  
0.0017 Kg / 0.06 oz

### Cable

Cable type:

EZ\_86-TP/M17

### Cable Entry

Centre contact:  
Outer contact:

soldered  
soldered

### Electrical Data

Impedance:  
Interface frequency max.:

50Ω  
6 GHz

### Piece Parts

Center contact:  
Outer contact:  
Body:

### Material

Copper Beryllium Alloy  
Brass  
Brass

### Surface Plating

Gold Plating (Nickel underplated)  
Gold Plating (Nickel underplated)  
Gold Plating (Nickel underplated)

Insulator:

PFA / PTFE

Fastening nut:  
Washer:

Brass  
Bronze

Gold Plating (Nickel underplated)  
Gold Plating (Nickel underplated)

### Attachments

Outline drawing:  
Catalogue drawing:  
Assembly instruction:

DOU-00009837  
DCA-00009839  
DOC-0000180183

### Notes

Mounting hole:  
Order as **24\_MCX-50-2-3/111\_NE**

DOU-00008855  
for Single

#### WAIVER!

While the information contained in this folder has been carefully compiled to the best of our present knowledge, it is not intended as representation or warranty of any kind on our part regarding the fitness of the products concerned for any particular use or purpose and neither shall any statement contained herein be construed as a recommendation to infringe any industrial property rights or as a license to use any such rights. The fitness of each product for any particular purpose must be checked beforehand with our specialists.

Issued: 17.12.03 15:59

Document: DOC-0000186801

RF\_Ca\_Pa\_C\_PDF

**uncontrolled copy**

Page 1



**HUBER+SUHNER**

HUBER+SUHNER AG  
Interconnect Division  
CH-9100 Herisau  
Phone +41 (0)71 353 41 11  
Fax +41 (0)71 353 45 90  
<http://www.hubersuhner.com>