

Honeywell Sensing and Control

Search


[narrow your search](#)

Products

- Controls Monitoring and Lighting (354)
- Machine Safety (1726)
- Sensors (7016)
- Switches (9736)

Technology

- Control and Instrumentation (1063)
- Electromechanical (9297)
- Microstructure (2298)
- Optical/Infrared (1077)
- Thick Film (1764)
- More...

143-201FAG-RC1 Discrete Thermistors

(Home : Products)



143 Series, 5,08 mm [0.2 in] disc thermistor with leads, 200 Ohm resistance, $\pm 10.0\%$ tolerance, 25/85 BETA = 3468

Actual product appearance may vary.

[Sales & Service](#)
[Distributor Inventory](#)

Need Help?

[Click here to contact us](#)
[Overview](#)
[Specs](#)
[Documentation](#)
[Application Notes](#)

Product Specifications

Availability	Global
Resistance	200 Ohm
Tolerance	$\pm 10.0\%$
Accuracy	25 °C [77 °F]
Beta	3468
Operating Temperature	-60 °C to 125 °C [-76 °F to 257 °F]
Diameter	5,08 mm [0.20 in]
Termination Material	Tinned copper
Lead Length	38,1 mm [1.50 in]
Time Constant in Air	16.0 s
Dissipation Constant	4,0 m/W°C
Series Name	143