

--

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		APPROVALS		DATE		Amphenol Connex							
8						DRAWN	G.R.S.	02/25/08									
7						UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm				PART DESCRIPTION N JACK TO TNC JACK ADAPTER							
6						UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”											
5																	
4	GASKET	SILICONE	RED	1		SHEET		1 OF 1		PART NO. 242132							
3	CONTACT PIN	PHOS. BRONZE	GOLD	1		CAD FILE C:/242/242132.DWG											
2	INSULATOR	PTFE	NATURAL	1		DWG. NO.				242132.DWG		REV.	B	SIZE	A	SCALE	NA
1	BODY	BRASS	NICKEL	1													
	DESCRIPTION	MATERIAL	FINISH	QTY		DO NOT SCALE DRAWING											