



Product Number: NBF-32010
UL/NEMA/IEC NBF Series – Solid Door Plastic Boxes



Design Features

- Designed to IP66 of IEC 529 and NEMA 1, 2, 4, 4x, 12 and 13 specifications
- All plastic construction including hinge pins
- Comes complete with stainless steel wall mounting brackets and hardware
- Style A has two or 3 plastic latches
- **Indoor Versions:**
 - ABS plastic enclosures are molded out of light gray material with UL94-HB Flammability rating. (Not UL Listed)
 - ABS/PC blended plastic enclosures are molded out of light gray material with UL94-5VA flammability rating. Suggested service temperature range - 40C to +70C.
 - Clear doors, for all models, are molded out of Polycarbonate material with UL94-V0 flammability rating.
- **Outdoor Versions:**
 - PC/PBT blended plastic enclosures are molded out of light gray material with UL94-5VA flammability and UV stabilized

Nominal External Dimensions Inches (Milimeters):

- A: 5.90" (150 mm)
- B: 5.90" (150 mm)
- C: 3.54" (90 mm)
- D: 2.76" (70 mm)

Actual Internal Dimensions Inches (+/- 0.06):

- E: 5.22"
- F: 5.22"
- G: 3.31"

Weight:

- 0.8 Lbs