



| LOC |    | DIST |   | REVISIONS |     |                      |  |  |         |       |
|-----|----|------|---|-----------|-----|----------------------|--|--|---------|-------|
| G   | 86 | P    | F | ZONE      | LTR | DESCRIPTION          |  |  | DATE    | APPD  |
|     |    |      |   |           |     |                      |  |  |         |       |
|     |    |      |   |           | S   | REV PER 063A-0561-01 |  |  | 080CT02 | JR MS |
|     |    |      |   |           |     |                      |  |  |         |       |



- 1 CIRCULAR MIL RANGE: 450-550 MCM  
2 TIN PL 0.00381 [0.000150] MIN THK PER MIL-T-10727



DO NOT SCALE PRINT.  
UNLESS SPECIFIED  
DIMENSIONS IN mm [INCHES]  
TOLERANCES ON :  
2 PLC DEC ± 0.51 [.020]  
3 PLC DEC ± -  
ANGLES ± -  
MATERIAL  
ANNEALED COPPER  
ASTM B-75

DR 11/22/91  
DK SCHRUM  
CHK 11/25/91  
AJ KAUFMAN  
APPD 11/25/91  
WJ VOCKROTH  
APPD 11/25/91  
AJ ADELMANN  
PRODUCT SPEC  
-

**AMP** AMP Incorporated  
Harrisburg, PA 17105-3608  
NAME  
TERMINAL, AMPPOWER™  
WIRE SIZE: 253.0mm<sup>2</sup> [500] MCM

FINISH



APPLICATION SPEC

-

WEIGHT .322 LB

SIZE



CAGE CODE

00779

DRAWING NO

326105

SCALE

2:1

SHEET

1 OF 1

METRIC