



TCSD-08-D-02.00-01-N-R

(2,00 mm) .0787"

TCSD SERIES

TIGER EYE™ IDC SOCKET CABLE

Mates with:

TMM, TMMH, STMM,
MMT, TW, MTMM, EHT,
ETMM (-SR), ZSTMM

SPECIFICATIONS

For complete specifications
see www.samtec.com?TCSD

Insulator Material:

Black Glass Filled Polyester

Contact:

BeCu

Plating:

Au or Sn over 50µ" (1,27 µm) Ni

Wire:

28 AWG 7/36 Stranded,

Tinned, Copper with

Gray PVC Insulator

Current Rating (TCSD/STMM):

2.8 A per pin

(1 pin powered per row)

Operating Temp Range:

-40°C to +105°C

Lead Size Accepted:

(0,48 mm) .019" to

(0,53 mm) .021"

Contact Resistance:

15 mΩ

Insertion Depth:

(2,87 mm) .113" to

(3,17 mm) .125"

RoHS Compliant:

Yes

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality



FILE NO. E111594













ALSO AVAILABLE (MOQ Required)

- Other sizes
 - Other platings
- Contact Samtec.



POLARIZING KEY

Specify PK-01-07 for
polarizing key (Available
in wheels of six each).
Also polarizes SMM
Series socket strips.

Note: TCSD Series
assemblies are non-
standard, non-returnable.



EJECTOR HEADERS & LOCKING CLIPS



See EHT Series.

WWW.SAMTEC.COM

Due to technical progress, all designs, specifications and components are subject to change without notice.